


CLAMPING PARTS OVERVIEW

	Article-group	Thread sizes						further sizes	Image	Description	Article-group	Thread sizes						further sizes
		M6	M8	M10	M12	M16	M20					M24	M6	M8	M10	M12	M16	
	EH 22540. EH 22570.	•	•	•	•	•	•			EH 23250. EH 23251.	•	•	•	•				
	EH 22680. EH 22690. EH 22691.	•	•	•	•	•	•			EH 23290.	•		•	•			•	
	EH 22800. EH 22810.		•		•					EH 23220.		•		•	•		•	
	EH 22730. EH 22740. EH 22731. EH 22741.	•	•	•	•	•	•	•		EH 23220.			•					
	EH 22700. EH 22710. EH 22720.	•	•	•	•	•	•	•		EH 23320.			•	•				
	EH 22760.	•	•	•	•			•		EH 23260. EH 23270. EH 23271. EH 23380. EH 23390. EH 23400. EH 23410.	•	•	•	•	•		•	
	EH 23010. EH 23020.	•	•	•	•	•	•	•		EH 23310. EH 23370.		•		•	•		•	
	EH 23030. EH 23040.	•	•	•	•	•	•	•		EH 23310.		•		•	•	•	•	
	EH 23050.	•	•	•	•	•	•	•		EH 23330.	•	•		•			•	
	EH 23060. EH 23061. EH 1007. EH 1107. EH 1108. EH 1617.			•	•	•	•	•		EH 23690.				•	•			
	EH 23070. EH 23080. EH 23090.	•	•	•	•	•	•	•		EH 23340.	•	•	•	•	•		•	
	EH 23140. EH 23150. EH 23160. EH 23170. EH 23180. EH 23190. EH 23200.			•	•	•	•	•		EH 1013. EH 1113. EH 1513. EH 1613.		•		•	•			
	EH 23185.			•	•	•	•	•		EH 1114. EH 1047. EH 1147. EH 1550. EH 1650.				•	•			
	EH 23700.				•	•				EH 23210. EH 1047. EH 1147. EH 1547. EH 1647.		•		•	•	•	•	
	EH 23210. EH 23211.		•		•	•				EH 23281. EH 1014. EH 1114. EH 1614.		•		•	•	•		
	EH 23230.				•	•	•			EH 23111.	16	20	25	30				
	EH 23231. EH 1137. EH 1138.				•	•												



Details and your contact persons
refer to:
www.halder.com/ClampingParts