

平压花姆指螺帽 · DIN 653

EH 24770.



产品描述

Knurled thumb screws are very versatile. Three material versions for the different requirements

- steel, blackened
- steel, zinc-plated by galvanization
- stainless steel

are available.

Knurled thumb screws can be easily tightened and released by hand. The ribbed outer surface of the nut prevents slipping when tightening / releasing with the fingers.

所有滚花螺丝是整体都有螺纹的一体成型制品 (DIN-代号 A)。

材质

- 钢、染黑、品质 5.8
- Steel, zinc-plated by galvanization, quality 5.8
- 不锈钢 1.4305, 钝化喷砂

更多信息


注意事项

根据 DIN 规范, 压花的间距和深度也不同。

更多产品

- 高压花的手转螺丝, DIN 464


图面



订单信息

d ₁	l	尺寸 [mm]	d ₂	k	重量 [g]	品号
钢、染黑、品质 5.8						
M 3	6		12	2,5	2,3	24770.0072
M 3	8		12	2,5	2,4	24770.0073
M 3	10		12	2,5	2,5	24770.0074
M 3	16		12	2,5	2,7	24770.0077
M 3	20		12	2,5	2,9	24770.0079
M 4	8		16	3,5	5,6	24770.0092
M 4	10		16	3,5	5,7	24770.0093
M 4	12		16	3,5	6,1	24770.0094
M 4	16		16	3,5	6,2	24770.0096
M 4	20		16	3,5	6,6	24770.0098
M 4	25		16	3,5	7,1	24770.0100
M 5	10		20	4,0	10,0	24770.0112
M 5	12		20	4,0	11,0	24770.0113
M 5	16		20	4,0	12,0	24770.0115
M 5	20		20	4,0	12,0	24770.0117
M 5	25		20	4,0	12,0	24770.0119
M 5	30		20	4,0	13,0	24770.0121
M 6	12		24	5,0	18,0	24770.0132
M 6	16		24	5,0	20,0	24770.0134
M 6	20		24	5,0	21,0	24770.0136

d ₁	l	尺寸		k	[g]	品号
		[mm]				
M 6	25		24	5,0	21,0	24770.0138
M 6	30		24	5,0	22,0	24770.0140
M 6	40		24	5,0	23,0	24770.0142
M 8	16		30	6,0	36,0	24770.0152
M 8	20		30	6,0	37,0	24770.0154
M 8	25		30	6,0	39,0	24770.0156
M 8	30		30	6,0	40,0	24770.0158
M 8	35		30	6,0	42,0	24770.0160
M 8	40		30	6,0	44,0	24770.0161
M10	20		36	8,0	71,0	24770.0172
M10	25		36	8,0	72,0	24770.0174
M10	30		36	8,0	76,0	24770.0176
M10	35		36	8,0	78,0	24770.0178
M10	40		36	8,0	80,0	24770.0180
钢, 镀锌						
M 3	6		12	2,5	2,0	24770.0472
M 3	8		12	2,5	2,0	24770.0473
M 3	10		12	2,5	3,0	24770.0474
M 3	16		12	2,5	3,0	24770.0477
M 3	20		12	2,5	3,0	24770.0479
M 4	8		16	3,5	6,0	24770.0492
M 4	10		16	3,5	6,0	24770.0493
M 4	12		16	3,5	6,0	24770.0494
M 4	16		16	3,5	7,0	24770.0496
M 4	20		16	3,5	7,0	24770.0498
M 4	25		16	3,5	7,0	24770.0500
M 5	10		20	4,0	10,0	24770.0512
M 5	12		20	4,0	11,0	24770.0513
M 5	16		20	4,0	12,0	24770.0515
M 5	20		20	4,0	12,0	24770.0517
M 5	25		20	4,0	14,0	24770.0519
M 5	30		20	4,0	13,0	24770.0521
M 6	12		24	5,0	19,0	24770.0532
M 6	16		24	5,0	19,0	24770.0534
M 6	20		24	5,0	20,0	24770.0536
M 6	25		24	5,0	20,0	24770.0538
M 6	30		24	5,0	20,0	24770.0540
M 6	40		24	5,0	23,0	24770.0542
M 8	16		30	6,0	35,0	24770.0552
M 8	20		30	6,0	38,0	24770.0554
M 8	25		30	6,0	35,0	24770.0556
M 8	30		30	6,0	35,0	24770.0558
M 8	35		30	6,0	43,0	24770.0560
M 8	40		30	6,0	40,0	24770.0561
M10	20		36	8,0	72,0	24770.0572
M10	25		36	8,0	74,0	24770.0574
M10	30		36	8,0	76,0	24770.0576
M10	35		36	8,0	76,0	24770.0578
M10	40		36	8,0	80,0	24770.0580
不锈钢 1.4305						
M 4	8		16	3,5	5,6	24770.0292
M 4	10		16	3,5	5,7	24770.0293
M 4	12		16	3,5	6,1	24770.0294
M 4	16		16	3,5	6,2	24770.0296
M 5	10		20	4,0	10,0	24770.0312
M 5	12		20	4,0	11,0	24770.0313
M 5	16		20	4,0	12,0	24770.0315
M 5	20		20	4,0	12,0	24770.0317
M 6	12		24	5,0	18,0	24770.0332
M 6	16		24	5,0	20,0	24770.0334
M 6	20		24	5,0	21,0	24770.0336
M 6	25		24	5,0	21,0	24770.0338

d ₁	l	尺寸		k	 [g]	品号
			d ₂			
M 8	16		30	6,0	36,0	24770.0352
M 8	20		30	6,0	37,0	24770.0354
M 8	25		30	6,0	39,0	24770.0356
M 8	30		30	6,0	40,0	24770.0358
M10	20		36	8,0	71,0	24770.0372
M10	25		36	8,0	72,0	24770.0374
M10	30		36	8,0	76,0	24770.0376
M10	40		36	8,0	80,0	24770.0380

遵守

For detailed compliance information please select the desired article number.