

THE SPECIALIST FOR PRECISE AND GENTLE WORK




LOCKSMITH'S HAMMER REDUCED REBOUND



HALDER

german
brand
award
19
gold



PUNCHES/DROP-MALLETS

- The little helpers for maintenance in an environment of limited accessibility
- Dead Blow – Ø 20/30/40/50 mm
- Replaceable inserts made of hard extruded nylon: **No chipping** (even at temperatures below zero), will not crack
- Replaces Brass Tip Drift Punches



Art.-No.	Ø [mm]	[g]	[mm]
3408.010	10	90	168
3408.012	12	130	170
3408.015	15	200	175
3408.020	20	215	150
3408.030	30	470	155
3408.040	40	785	160
3408.050	50	1.250	165

MAXXCRAFT SERIES 3666

- Noticeable reduced rebound and thus full transmission of the power of impact onto the workpiece, caused by patented rubber connection between head and handle
- Reduced rebound (minus 69%)
- Higher impact (plus 24%)
- Protective handle sleeve with rubber coating
- According to DIN 1041



Art.-No.	[g]	[mm]
3666.003	300	300
3666.005	500	320
3666.008	800	350
3666.010	1.000	360

SECURAL SERIES 3380

- The specialist for corners and edges
- **Maximum rebound damping**
- Absolutely unbreakable connection
- Interchangeable inserts made of polyurethane: rectangular, medium-hard, noise-dampening, impact cushioning, wear-resistant




Art.-No.	Length x Width [mm]	[g]	[mm]
3380.040	30 x 40	680	300
3380.045	35 x 45	1.000	310

ERWIN HALDER KG

Erwin-Halder-Straße 5-9
88480 Achstetten-Bronnen
Germany

T +49 7392 7009-0
F +49 7392 7009-160
info@halder.com
www.halder.com

Distributed by:



GB/EH/07/2020

THE ORIGINAL FOR PROFESSIONALS

AUTOMOTIVE / INDUSTRY



103.151

ASSEMBLY / REPAIR / MAINTENANCE WORK



STRAIGHTENING WORK / WHEEL CHANGE

POSITIONING AND ADJUSTING OF WORKPIECES

SIMPLEX SERIES 3749

- All parts are replaceable
- **High impact strength** (due to additional increase in weight)
- **High stability** (reinforced cast iron housing, fibre-glass handle)
- Replaces conventional copper and lead mallets
- 2 different inserts: Copper (hard) / Soft metal (silver, hard, heat-resistant)

Art.-No.	Ø [mm]	■ [g]	▬ [mm]
3749.030	30	590	300
3749.040	40	1.195	330

SIMPLEX SERIES 3028

- All parts are replaceable
- High quality wood handle
- Robust and extremely durable cast iron housing
- 2 different inserts: Rubber composition (black, medium hard, impact cushioning, odorless, low-wear hardness) / Nylon (white, hard, very wear-resistant, **no chipping**, oil and grease resistant)

Art.-No.	Ø [mm]	■ [g]	▬ [mm]
3028.030	30	355	295
3028.040	40	650	325
3028.050	50	1.140	370
3028.060	60	1.520	405
3028.080	80	2.890	490

DEAD BLOW SLEDGE HAMMER SUPERCRAFT SERIES 3366.VS

- **Non-rebound, high impact**
- Vibration-reducing hickory handle
- No mushrooming or shrapnel when hitting steel stakes or pins
- Replaceable inserts made of hard extruded nylon: **No chipping** (even at temperatures below zero), will not crack

Art.-No.	Ø [mm]	■ [g]	▬ [mm]
3366.081	80	4.410	880
3366.100	100	7.050	1.000
3366.107	100	9.300	1.000

BLACKCRAFT SERIES 3379

- **Non-rebound, high impact**
- Fully sheathed with polyurethane
- Prevents scratches as well as sparking in case of failures
- Completely robot welded
- With ergonomic, anti-slip and break-proof steel tube handle

Art.-No.	Ø [mm]	■ [g]	▬ [mm]
3379.040	40	640	300
3379.050	50	900	310
3379.060	60	1.300	315

SUPERCRAFT SERIES 3389

- **Non-rebound, high impact**
- Ergonomic, anti-slip and break-proof three-component handle
- Replaceable inserts made of hard extruded nylon: **No chipping** (even at temperatures below zero), will not crack

Art.-No.	Ø [mm]	■ [g]	▬ [mm]
3389.040	40	790	370
3389.050	50	1.040	380
3389.060	60	1.625	390

SUPERCRAFT SERIES 3377

- **Non-rebound, high impact**
- Break-proof steel tube handle and ergonomic, anti-slip grip
- Replaceable inserts made of hard extruded nylon: **No chipping** (even at temperatures below zero), will not crack

Art.-No.	Ø [mm]	■ [g]	▬ [mm]
3377.025	25	385	270
3377.030	30	585	295
3377.040	40	805	305
3377.050	50	1.150	315
3377.060	60	1.750	325
3377.070	70	2.250	335