# Mounting Pads 22590.0024



# **Product Description**

Mounting pads can be used as foot or thrust pad. Not parallel bearing surfaces up to 15° degrees can be compensated.

# Material

# **Ball element**

· Heat-treated steel, tempered, blackened

# Pad


· Heat-treated steel, blackened


# More information

# Notes

For the versions  $d_1$  = M10 and M12 the lock nut conforms to DIN 934.

# **Drawing**






# **Order information**

Dimensions					ws	Load capacity for static load		ă	Art. No.
d <sub>1</sub>	d <sub>2</sub>	h₁ ~	h <sub>2</sub>	t		max.	max.		
[mm]					[mm]	[kN]	[°C]	[9]	
pad and ball element – picture 1, Heat-treated steel									
M24	60	45	9.5	19	36	65	250	498	22590.0024



Page 1 of 2 www.halder.com Published on: 10.8.2024

# **Application example**



# Compliance

# **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Erwin Halder KG

# **Does not contain Proposition 65 substances**

No Proposition 65 substances included.

https://www.P65Warnings.ca.gov/

# **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024

www.halder.com