# Adjustable Clamping Levers • inner parts from stainless steel, with screw 24390.0664



## **Product Description**

Adjustable clamping levers with rust-proof inner parts. Suitable for multiple applications, e.g. medical environments, chemical industry, and so on.

## Material

Lever

 Zinc die-cast, plastic coated, black, similar to RAL 9005, matt structure

#### Inner parts

Stainless steel 1.4305

## Screw

Stainless steel 1.4305

## Operation


**By lifting the lever** the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

#### More information

#### Notes

The screw part can be exchanged.


Drawing



## **Order information**

d <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>	d <sub>3</sub>	Dimensions h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	l <sub>2</sub>	<b>i</b>	Art. No.
				[mm]					[9]	
black	·									
30	M16	50	23	50.5	12	5	76	108	370	24390.0664

# Application example



# Compliance

## **RoHS compliant**

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

**Contains Proposition 65 substances** 



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

# Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.