Rubber Endstop Buffers • cylindrical 25150.0482



Product Description

To be used as an elastic end-stop, bearing foot etc. The hardness is 55 \pm 5° shore A. Further shore hardnesses (40 \pm 5° shore A and 70 \pm 5° shore A) on request.

Material

Support washer

Steel, zinc-plated, blue chromated

Body

• Rubber natural caoutchouc (NR), black

Screw


· Steel, zinc-plated, blue chromated


More information

Further products

· Support Legs, impact cushioning

Drawing






picture 1

picture 2

Order information

d ₁	Dimensions			Spring rate R ~	Load capacity max.	Spring range ~	min.	max.	i	Art. No.	
	[mm]				[N/mm]	[N]	[mm]	[°C]		[g]	
with screw – picture 2, Steel											
100	40	M16	41	3	810	8100	10	-30	80	570	25150.0482

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

