Rubber Metal Buffers • cylindrical

25150.0221



Product Description

To be used for elastic bearing of motors, compressors, pumps etc.

The hardness is 55 \pm 5° shore A. Further shore hardnesses (40 \pm 5° shore A and 70 \pm 5° shore A) on request.

Material

Support washer

Steel, zinc-plated, blue chromated

Threaded bushing

• Steel, zinc-plated, blue chromated


Body


• Rubber natural caoutchouc (NR), black

Screw

• Steel, zinc-plated, blue chromated

Drawing






Order information

Dimensions					Spring rate R	Load capacity max.	Spring range			I	Art. No.
d ₁ ±1.5	l₁ ±1.5	d ₂	l ₂	s		max.		min.	max.		
[mm]					[N/mm]	[N]	[mm]	[°C]		[g]	
with screw, on both sides – picture 3											
20	15	M6	18	2	94	352	3.75	-30	80	18	25150.0221



www.halder.com Page 1 of 2
Published on: 10.8.2024

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024