Rubber Endstop Buffers • cylindrical 25150.0431



Product Description

To be used as an elastic end-stop, bearing foot etc. The hardness is 55 \pm 5° shore A. Further shore hardnesses (40 \pm 5° shore A and 70 \pm 5° shore A) on request.

Material

Support washer

Steel, zinc-plated, blue chromated

Body

• Rubber natural caoutchouc (NR), black

Screw


· Steel, zinc-plated, blue chromated


More information

Further products

· Support Legs, impact cushioning

Drawing






picture 1

picture 2

Order information

	Dimensions			Spring rate R ~	Load capacity max.	Spring range ~			Ĩ	Art. No.	
d ₁	4	d ₂ [mm]	I ₂	S	[N/mm]	[N]	[mm]	min. max. [°C]		[9]	
with screw – picture 2, Steel											
30	15	M8	20	2	294	934	3.75	-30	80	28	25150.0431

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

