# Rubber Endstop Buffers · cylindrical 25150.1443



## **Product Description**

To be used as an elastic end-stop, bearing foot etc. The hardness is 55 ±5° shore A. Further shore hardnesses (40 ±5° shore A and 70 ±5° shore A) on request.

## **Material**

## Support washer

Stainless steel 1.4301

## Body

• Rubber natural caoutchouc (NR), black

# Screw


· Stainless steel 1.4301


#### More information

#### **Further products**

· Support Legs, impact cushioning

### Drawing






picture 1

picture 2

## Order information

Dimensions					Spring rate R Load capacity Spr	Spring range	ring range		Ĭ	Art. No.	
d <sub>1</sub>	I <sub>1</sub>	d <sub>2</sub>	I <sub>2</sub>	s	~	max.	~	min.	max.	_	
	[mm]			[N/mm]	[N]	[mm]	[°C]		[g]		
with screw – picture 2, Stainless steel											
40	30	M8	23	2	213	1600	7.5	-30	80	73	25150.1443

## **Application example**



## Compliance

## **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

## Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

#### **Does not contain Proposition 65 substances** No Proposition 65 substances included.

https://www.P65Warnings.ca.gov/

## Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.