


SPRING PLUNGERS

METRIC MODELS




CALCULATION OF THE INDEXING RESISTANCE



$$F_x = \frac{F}{\tan \frac{\alpha}{2}}$$

Sample calculation for:
 $\alpha = 60^\circ, F_x = 1,732 \times F$
 $\alpha = 90^\circ, F_x = F$
 $\alpha = 120^\circ, F_x = 0,577 \times F$




standard spring load



heavy spring load




www.halder.com/SpringPlungers-Video




CERTIFIED

Certified spring load F1 and F2 and stroke s.



PREMIUM QUALITY

First-rate quality and minimum wear thanks to the use of hardened pins.



SECURE

Outstanding functional reliability thanks to - among other things - the assembly procedure used and a specific manufacturing process.



CLEAR

Coherent, uniform and clearly visible identification of the spring load thanks to a permanent marking on the body.