

## Spring Plungers · smooth, with collar and ball, self-clamping – INCH

2B080.0060



### Product Description

Spring plungers can be used for locating or for applying pressure, as a detent or for ejection. The spring plungers compensate tolerances of up to 0.008" (inches) of the locating hole by self-clamping. This saves costs in the machining of the locating hole.

### Material

#### Body

- Thermoplastic POM, black

#### Ball

- Stainless steel, hardened

#### Spring

- Stainless steel

### Assembly

Thanks to the flexible design of the body, a direct manual mounting and a secure overhead installation is possible.

### More information

### Notes

Customized design on request.  
Spring plungers are specially tested for spring range and forces.


### References

Calculation of indexing resistance, please refer to appendix - Technical Data -

### Further products

- Spring Plungers, smooth, with collar and ball, self-clamping
- Locators, with bore hole, for spring plungers
- Locators, smooth, for spring plungers

### Drawing



### Order information

Dimensions					Stroke s	Spring load <sup>1)</sup>		Temperature		Location hole D <sub>1</sub> +0.008	oz	Art. No.
d <sub>1</sub> +0.004	d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub> ±0.01	l <sub>2</sub>		F <sub>1</sub> ~	F <sub>2</sub> ~	min.	max.			
[in]					[in]	[lb]		[°F]		[in]	[oz]	
1/4	0.197	0.276	0.276	0.039	0.059	1.4	2.8	-22	122	1/4	0.024	2B080.0060

<sup>1)</sup> statistical average value

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.