Spring Plungers • smooth, without collar 22080.0306



Product Description

Spring plungers can be used for locating or for applying pressure, as a detent or for ejection.

Material

Body

· Stainless steel 1.4305

· Stainless steel, hardened

Spring

Stainless steel

Assembly

The locating hole has to be adapted to each individual application case. We recommend an F8 size location hole for easy assembly and a H9 size when tight fit is required.

Characteristic

Standard spring load: no marking





Standard spring load

Heavy spring load

More information

Notes

Special types on request.


Spring plungers are specially tested for spring range and forces.

Calculation of indexing resistance, please refer to appendix - Technical Data -

Further products

- Spring Plungers, smooth, without collar, with moveable ball
- Locators, with bore hole, for spring plungers
- · Locators, smooth, for spring plungers

Drawing



Erwin Halder KG

Order information


d ₁	Dimensio	ons I	Stroke s	Spring F ₁	load ¹⁾	max.	Location hole joint connection F8 /	I	Art. No.
±0.04	[mm]	l	[mm]	~ [t	~ N]	[°C]	press fit H9 [mm]	[9]	
stainless steel, standard spring load									
2	1	3.5	0.3	0.8	1.5	250	2	0.1	22080.0306

¹⁾ statistical average value

www.halder.com Page 1 of 2

Published on: 10.8.2024

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Erwin Halder KG

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2

Published on: 10.8.2024