# **Spring Plungers •** smooth, without collar 22080.0358



# **Product Description**

Spring plungers can be used for locating or for applying pressure, as a detent or for ejection.

#### **Material**

### Body

Stainless steel 1.4305

#### Ball

· Stainless steel, hardened

## Spring

Stainless steel

#### Assembly

The locating hole has to be adapted to each individual application case. We recommend an F8 size location hole for easy assembly and a H9 size when tight fit is required.

#### Characteristic

Heavy spring load: marked with two lines



Heavy spring load

# Standard spring load

# More information

#### Notes

Special types on request. Spring plungers are specially tested for spring range and forces.


#### References

Calculation of indexing resistance, please refer to appendix - Technical Data -

#### **Further products**

- Spring Plungers, smooth, without collar, with moveable ball
- · Locators, with bore hole, for spring plungers
- Locators, smooth, for spring plungers

# Drawing




# Order information

۲ d <sub>1</sub> ±0.04	Dimensions	I	Stroke s	Spring F1 ~	y load <sup>1)</sup> F <sub>2</sub> ~	max.	Location hole joint connection F8 / press fit H9	Ă	Art. No.
[mm]			[mm]	[N]		[°C]	[mm]	[9]	
stainless steel, heavy spring load									
2.5	1.5	5	2.5	4.7	7.1	250	2.5	0.1	22080.0358

<sup>1)</sup> statistical average value

# Application example



# Compliance

# **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

# Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.