

## Tornillos Moleteados Altos · DIN 464

EH 24790.



### Descripción del Producto

Knurled thumb screws are very versatile. Three material versions for the different requirements

- steel, blackened
- steel, zinc-plated by galvanization
- stainless steel

are available.

Knurled thumb screws can be easily tightened and released by hand. The ribbed outer surface of the nut prevents slipping when tightening / releasing with the fingers.

Todos los tornillos moleteados están realizados en una sola pieza. Contrariamente a la Hoja Estándar Oficial, todos tienen rosca hasta la cabeza y con una salida sin entalladura en el extremo de la rosca. Por lo tanto, los tornillos no se pueden atornillar hasta el fondo de la cabeza.

### Material

- Acero, pavonado, calidad 5.8
- Acero, cincado por galvanización, calidad 5.8
- Acero inoxidable 1.4305, mate

### Más información


#### Notas

El paso de rosca y profundidad del moleteado pueden diferir de la norma DIN.

#### Otros productos


- Tornillos Moleteados Planos, DIN 653


### Dibujo






### Información para el pedido

d <sub>1</sub>	l	d <sub>2</sub>	Dimensiones			[g]	Referencia
			d <sub>3</sub>	h	k		
[mm]							
<b>Acero, pavonado, calidad 5.8</b>							
M 3	6	12	6	7,5	2,5	3,7	<a href="#">24790.0074</a>
M 3	10	12	6	7,5	2,5	3,8	<a href="#">24790.0076</a>
M 3	12	12	6	7,5	2,5	4,0	<a href="#">24790.0077</a>
M 3	16	12	6	7,5	2,5	4,0	<a href="#">24790.0079</a>
M 3	20	12	6	7,5	2,5	4,5	<a href="#">24790.0081</a>
M 4	5	16	8	9,5	3,5	7,7	<a href="#">24790.0092</a>
M 4	8	16	8	9,5	3,5	8,0	<a href="#">24790.0094</a>
M 4	10	16	8	9,5	3,5	8,1	<a href="#">24790.0095</a>
M 4	12	16	8	9,5	3,5	8,6	<a href="#">24790.0096</a>
M 4	16	16	8	9,5	3,5	8,4	<a href="#">24790.0098</a>
M 4	20	16	8	9,5	3,5	9,1	<a href="#">24790.0100</a>
M 4	25	16	8	9,5	3,5	9,0	<a href="#">24790.0102</a>
M 5	6	20	10	11,5	4,0	14,0	<a href="#">24790.0112</a>
M 5	8	20	10	11,5	4,0	15,0	<a href="#">24790.0113</a>
M 5	10	20	10	11,5	4,0	15,0	<a href="#">24790.0114</a>
M 5	12	20	10	11,5	4,0	15,0	<a href="#">24790.0115</a>

d <sub>1</sub>	l	Dimensiones			h	k		Referencia
		d <sub>2</sub>	d <sub>3</sub>	[mm]				
M 5	16	20	10	11,5	4,0	16,0	24790.0117	
M 5	20	20	10	11,5	4,0	16,0	24790.0119	
M 5	25	20	10	11,5	4,0	17,0	24790.0121	
M 5	30	20	10	11,5	4,0	17,0	24790.0123	
M 6	8	24	12	15,0	5,0	28,0	24790.0132	
M 6	10	24	12	15,0	5,0	27,0	24790.0133	
M 6	12	24	12	15,0	5,0	28,0	24790.0134	
M 6	16	24	12	15,0	5,0	28,0	24790.0136	
M 6	20	24	12	15,0	5,0	29,0	24790.0138	
M 6	25	24	12	15,0	5,0	30,0	24790.0140	
M 6	30	24	12	15,0	5,0	31,0	24790.0142	
M 6	35	24	12	15,0	5,0	31,0	24790.0144	
M 8	12	30	16	18,0	6,0	53,0	24790.0152	
M 8	16	30	16	18,0	6,0	55,0	24790.0154	
M 8	20	30	16	18,0	6,0	56,0	24790.0156	
M 8	25	30	16	18,0	6,0	58,0	24790.0158	
M 8	30	30	16	18,0	6,0	60,0	24790.0160	
M 8	35	30	16	18,0	6,0	62,0	24790.0162	
M 8	40	30	16	18,0	6,0	61,0	24790.0164	
M10	15	36	20	23,0	8,0	104,0	24790.0171	
M10	20	36	20	23,0	8,0	106,0	24790.0173	
M10	25	36	20	23,0	8,0	109,0	24790.0175	
M10	30	36	20	23,0	8,0	112,0	24790.0177	
M10	35	36	20	23,0	8,0	116,0	24790.0179	
M10	40	36	20	23,0	8,0	116,0	24790.0181	
<b>Acero, cincado por galvanización</b>								
M 3	6	12	6	7,5	2,5	4,0	24790.0474	
M 3	8	12	6	7,5	2,5	4,0	24790.0475	
M 3	10	12	6	7,5	2,5	4,0	24790.0476	
M 3	12	12	6	7,5	2,5	4,0	24790.0477	
M 3	16	12	6	7,5	2,5	5,0	24790.0479	
M 3	20	12	6	7,5	2,5	5,0	24790.0481	
M 4	5	16	8	9,5	3,5	9,0	24790.0492	
M 4	8	16	8	9,5	3,5	8,0	24790.0494	
M 4	10	16	8	9,5	3,5	8,0	24790.0495	
M 4	12	16	8	9,5	3,5	8,0	24790.0496	
M 4	16	16	8	9,5	3,5	8,0	24790.0498	
M 4	20	16	8	9,5	3,5	9,0	24790.0500	
M 4	25	16	8	9,5	3,5	9,0	24790.0502	
M 5	6	20	10	11,5	4,0	15,0	24790.0512	
M 5	8	20	10	11,5	4,0	15,0	24790.0513	
M 5	10	20	10	11,5	4,0	15,0	24790.0514	
M 5	12	20	10	11,5	4,0	14,0	24790.0515	
M 5	16	20	10	11,5	4,0	15,0	24790.0517	
M 5	20	20	10	11,5	4,0	16,0	24790.0519	
M 5	25	20	10	11,5	4,0	16,0	24790.0521	
M 5	30	20	10	11,5	4,0	17,0	24790.0523	
M 6	8	24	12	15,0	5,0	27,0	24790.0532	
M 6	10	24	12	15,0	5,0	27,0	24790.0533	
M 6	12	24	12	15,0	5,0	27,0	24790.0534	
M 6	16	24	12	15,0	5,0	28,0	24790.0536	
M 6	20	24	12	15,0	5,0	29,0	24790.0538	
M 6	25	24	12	15,0	5,0	28,0	24790.0540	
M 6	30	24	12	15,0	5,0	30,0	24790.0542	
M 6	35	24	12	15,0	5,0	31,0	24790.0544	
M 8	12	30	16	18,0	6,0	55,0	24790.0552	
M 8	16	30	16	18,0	6,0	55,0	24790.0554	
M 8	20	30	16	18,0	6,0	56,0	24790.0556	
M 8	25	30	16	18,0	6,0	58,0	24790.0558	
M 8	30	30	16	18,0	6,0	50,0	24790.0560	
M 8	35	30	16	18,0	6,0	63,0	24790.0562	
M 8	40	30	16	18,0	6,0	62,0	24790.0564	

d <sub>1</sub>	l	Dimensiones			h	k	 [g]	Referencia
		d <sub>2</sub>	d <sub>3</sub>	[mm]				
M10	12	36	20	23,0	8,0	105,0	<a href="#">24790.0570</a>	
M10	15	36	20	23,0	8,0	106,0	<a href="#">24790.0571</a>	
M10	20	36	20	23,0	8,0	107,0	<a href="#">24790.0573</a>	
M10	25	36	20	23,0	8,0	110,0	<a href="#">24790.0575</a>	
M10	30	36	20	23,0	8,0	112,0	<a href="#">24790.0577</a>	
M10	35	36	20	23,0	8,0	115,0	<a href="#">24790.0579</a>	
M10	40	36	20	23,0	8,0	116,0	<a href="#">24790.0581</a>	
<b>Acero inoxidable 1.4305</b>								
M 3	6	12	6	7,5	2,5	3,7	<a href="#">24790.0274</a>	
M 3	10	12	6	7,5	2,5	3,8	<a href="#">24790.0276</a>	
M 3	12	12	6	7,5	2,5	4,0	<a href="#">24790.0277</a>	
M 3	16	12	6	7,5	2,5	4,0	<a href="#">24790.0279</a>	
M 4	8	16	8	9,5	3,5	8,0	<a href="#">24790.0294</a>	
M 4	10	16	8	9,5	3,5	8,1	<a href="#">24790.0295</a>	
M 4	12	16	8	9,5	3,5	8,6	<a href="#">24790.0296</a>	
M 4	16	16	8	9,5	3,5	8,4	<a href="#">24790.0298</a>	
M 4	20	16	8	9,5	3,5	9,1	<a href="#">24790.0300</a>	
M 4	25	16	8	9,5	3,5	9,0	<a href="#">24790.0302</a>	
M 5	10	20	10	11,5	4,0	15,0	<a href="#">24790.0314</a>	
M 5	12	20	10	11,5	4,0	15,0	<a href="#">24790.0315</a>	
M 5	16	20	10	11,5	4,0	16,0	<a href="#">24790.0317</a>	
M 5	20	20	10	11,5	4,0	16,0	<a href="#">24790.0319</a>	
M 5	25	20	10	11,5	4,0	17,0	<a href="#">24790.0321</a>	
M 5	30	20	10	11,5	4,0	17,0	<a href="#">24790.0323</a>	
M 6	12	24	12	15,0	5,0	28,0	<a href="#">24790.0334</a>	
M 6	16	24	12	15,0	5,0	28,0	<a href="#">24790.0336</a>	
M 6	20	24	12	15,0	5,0	29,0	<a href="#">24790.0338</a>	
M 6	25	24	12	15,0	5,0	30,0	<a href="#">24790.0340</a>	
M 6	30	24	12	15,0	5,0	31,0	<a href="#">24790.0342</a>	
M 6	35	24	12	15,0	5,0	31,0	<a href="#">24790.0344</a>	
M 8	16	30	16	18,0	6,0	55,0	<a href="#">24790.0354</a>	
M 8	20	30	16	18,0	6,0	56,0	<a href="#">24790.0356</a>	
M 8	25	30	16	18,0	6,0	58,0	<a href="#">24790.0358</a>	
M 8	30	30	16	18,0	6,0	60,0	<a href="#">24790.0360</a>	
M 8	35	30	16	18,0	6,0	62,0	<a href="#">24790.0362</a>	

### Ejemplo de aplicación



### Cumplimiento

Para obtener información detallada sobre el cumplimiento, seleccione el número de artículo deseado.