Threaded Lifting Pins • self-locking, for centre holes according to DIN 332



Product Description

This threaded lifting pin is used when there is a threaded hole with a counterbore according to DIN 332.

Heavy-duty lifting element for quick and easy use, with moveable shackle and locking stud to provide protection against unintentional unlocking. For lifting loads, the threaded lifting pin is inserted into a threaded hole. In contrast to a ringbolt, time-consuming screwing in and out is therefore unnecessary.

All versions are corrosion-protected. The version made of stainless steel is also resistant to corrosion and weathering, so it is also suitable for external use. In addition, the high-strength, precipitation-hardened pin makes extreme loads possible.

Material

Pin part

· Stainless steel 1.4542, precipitationhardened

Press button

Aluminium, orange, anodised

Threaded element

· Stainless steel 1.4542, precipitationhardened

Shackle

· Stainless steel 1.4571

Spring

Stainless Steel





Assembly

Threaded lifting pins can be mounted into a thread that is true to gauge.

Mounting:

- 1. Press in the button and hold it down.
- 2. Insert the threaded lifting pin.
- 3. Release the button (The button must be back in its original position.).
- 4. Tighten the threaded lifting pin by hand, until it bears compleately on the bearing surface.
- 5. It must be ensured that the threaded segments are engaged in the mounting thread.

Dismantling:

- 1. Unscrew the threaded lifting pin approx. a quarter of a turn anticlockwise.
- 2. Press in the button and hold it down.
- 3. Remove the threaded lifting pin.
- 4. Release the button.

Operation

Each threaded lifting pin contains an instruction manual with an EC Declaration of Conformity.

More information


Further products

- · Lifting Pins, self-locking
- Lifting Pins, self-locking, stainless steel
- Threaded Lifting Pins, self-locking
- Threaded Lifting Pins, self-locking, with rotatable shackle
- Threaded Lifting Pins, self-locking INCH
- Threaded Lifting Pins, self-locking, with rotatable shackle - INCH



Erwin Halder KG www.halder.com Page 1 of 5 Published on: 10.8.2024

Drawing



Order information


	Dimensions														ad capa cording	g to	Locating thread	<u></u>	Ĭ	Art. No.
d ₁	I ₁	d ₂ -0.07	d ₃	d ₄	l ₂	l ₃	I ₄	l ₅	I ₆	I ₇	I ₈	l ₉	I ₁₀	F ₁	F ₂	F ₃		max.		
	[mm]														[kN]		[mm]	[°C]	[g]	
Stainle	Stainless steel																			
M20	25	17.75	30	20.7	31.8	39.1	53.7	32.6	36	56	109.2	30	17	10	7.7	5.8	M20	250	555	22352.3020

www.halder.com Page 2 of 5
Published on: 10.8.2024

Application example



www.halder.com Page 3 of 5
Published on: 10.8.2024



Page 4 of 5 Published on: 10.8.2024

www.halder.com

Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 5 of 5
Published on: 10.8.2024

Erwin Halder KG www.l