# Threaded Lock Pins · self-locking

22355.1503



### **Product Description**

Threaded lock pins are used for quick fastening, locking, adjusting, changing, clamping, connecting and securing. Quickly and easily unlockable for frequently repeated connections. By pressing the button, the threaded segments unlock and the threaded lock pin can be inserted into or removed from a threaded hole. A time-consuming screwing in and out is unnecessary. The threaded lock pin is characterised by the following features:

- · Corrosion-protected
- · No time-consuming screwing in and out
- · Self-locking due to spring load

### **Material**

### Pin part

· Stainless Steel

#### Handle

 Thermoplastic PA 6, black, dull similar to RAL 9005

### Press button

· Aluminium, orange, anodised

### Threaded element

 Stainless steel 1.4542, precipitationhardened

#### **Spring**

Stainless Steel

### **Assembly**

Threaded lock pins can only be mounted into a thread that is true to gauge.

### Mounting:

- 1. Press in the button and hold it down.
- 2. Insert the threaded lock pin.
- 3. Release the button (The button must be back in its original position.).
- 4. Tighten the threaded lock pin by hand as required.
- It must be ensured that the threaded segments are engaged in the mounting thread.

### Dismantling:

- 1. Unscrew the threaded lock pin approx. a guarter of a turn anticlockwise.
- 2. Press in the button and hold it down.
- 3. Remove the threaded lock pin.
- 4. Release the button.

### Operation

The threaded segments are unlocked by pressing the button.

## More information

### Notes

Special types on request.

Due to the thread geometry, the clamping force is higher with the smaller thread sizes.


### Accessories


Can easily be fitted with retaining cable EH 22355.

## **Further products**

- Threaded Lock Pins, self-locking, with axial bearing
- · Retaining Cables, for threaded lock pin

## Drawing








Erwin Halder KG www.halder.com Page 1 of 2

### **Order information**

			Dir	mensions	3			Locating thread			Tightenin¢lampin			Clampin	Ĭ	Shearing	Art. No.
d <sub>1</sub>	I <sub>1</sub>	<b>d</b> <sub>2</sub> -0.07	<b>d</b> <sub>3</sub>	d <sub>4</sub>	l <sub>2</sub>	l <sub>3</sub>	I <sub>4</sub>		min. max.	max.	force max.	tightening torque	force ~ <sup>2)</sup>		resistance, two-shear <sup>3)</sup> min.		
[mm]								[mm]	[°C]		[Nm]	[kN]	[Nm]	[kN]	[g]	[kN]	
Stainless Steel																	
M16	15	13.8	40	21.6	34	68.6	12	M16	-30	80	5	2.1	3.5	1.5	116	82.7	22355.1503

<sup>1)</sup> Average hand force established in trials.

## **Application example**



## Compliance

## **RoHS** compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

## Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

## **Contains Proposition 65 substances**



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

## **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 10.8.2024

<sup>&</sup>lt;sup>2)</sup> Average value established in trials.

<sup>&</sup>lt;sup>3)</sup> Shearing resistance similar to DIN 50141; values apply to applications in plugged condition (without applied tightening torque).