Clamp Lock Pins · with button handle

22410.0072



Product Description

For rapid fastening, locking, adjusting, replacing, and securing in blind holes (H11) without additional locating bushings.

Quick and easy to release for connections which are made repeatedly. Flexible use because the balls are clamped between bolt and hole.

All versions are corrosion resistant. When using stainless steel 1.4542: high-strength, hardened, abrasion resistant pin with high load capacity.

Material

Pin part

Stainless steel 1.4305

Handle

• Aluminium, black similar to RAL 9005

Press button

 Case-hardened steel, nitrided, yellow similar to RAL 1016

Spring

· Stainless steel

Assembly

Simple H11 boreholes are sufficient.

Mounting:

- 1. Press in the button and hold it down
- 2. Insert the lifting pin
- 3. Release the button (The button must be back in its original position)

Dismantling:

- 1. Press in the button and hold it down.
- 2. Remove the lifting pin.
- 3. Release the button.

Operation

Clamp lock pins can be used in blind holes. The holding forces achieved in an H11 borehole depends on the material of the counterpart:

- Steel, hardened min. 30 N
- · Steel, soft min. 120 N
- · Stainless steel, soft min. 120 N
- Al, aluminum alloy min. 250 N

More information

Notes

Special types on request.

The clamp lock pin must not be used for lifting loads


Accessories

Can easily be fitted with retaining cable EH 22400.

Further products

· Retaining Cables

Drawing



Erwin Halder KG

** Types from stainless steel 1.4542 with marking.

www.halder.com


Page 1 of 4 Published on: 10.8.2024

Order information

			ı	Dimens	ions			Holding	Location		}	I	Shearing resistance,	Art. No.	
d ₁ -0.04 -0.08	l ₁ +2 -1	d ₂ +0.1 -0.05	d ₃	d ₄	l ₂	l ₃	l ₄	l ₅	force ¹⁾ min. Steel, soft	hole H11	min.	max.		two-shear ²⁾ min.	
			l	[mm]		I	[N]	[mm]	[°	c]	[g]	[kN]		
Stainle	Stainless steel														
10	80	10.3	14.1	25	90	27.3	22.6	18.6	120	10	-30	150	70	60	22410.0072

¹⁾ The holding force depends on the material of the counterpart - for further values see "operation".


Application example





www.halder.com Page 2 of 4 Published on: 10.8.2024

²⁾ Shearing resistance similar to DIN 50141



Compliance

Non-RoHS compliant

Not compliant according to Directive 2011/65/EU and Directive 2015/863.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

Page 4 of 4 www.halder.com Published on: 10.8.2024