# Mounting Pads 22590.0206



# **Product Description**

Mounting pads can be used as foot or thrust pad. Not parallel bearing surfaces up to 15° degrees can be compensated.

### Material

#### **Ball element**

• Stainless steel 1.4305

#### Pad


• Stainless steel 1.4305


# More information

#### Notes

For the versions  $d_1$  = M10 and M12 the lock nut conforms to DIN 934.

# Drawing





# **Order information**


		Dimensions			ws	Load capacity for static load	<u>D</u> i	I	Art. No.
d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub> ~	h <sub>2</sub>	t		max.	max.		
		[mm]			[mm]	[kN]	[°C]	[g]	
pad and ball element – picture 1, Stainless steel									
М6	20	14	2.5	5	10	8	250	15	22590.0206



Erwin Halder KG

Page 1 of 2 www.halder.com Published on: 10.8.2024

# **Application example**



# Compliance

# **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Erwin Halder KG

#### **Does not contain Proposition 65 substances**

No Proposition 65 substances included.

https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024

www.halder.com