Ball-Ended Thrust Screws • headless, ball protected against rotating 22700.0844



Product Description

Ball-ended thrust screws can also be used for clamping, tightening or supporting of non-parallel surfaces.

The flat-faced, movable ball enables a flat load transmission.

Material

Ball

· Stainless steel, hardened

Screw

· Stainless steel 1.4305

More information

Notes

Ball protected against rotating. Special types on request.


References

Thread lock on request, please refer to appendix - Technical Data -

Further products

- Ball-Ended Thrust Screws, headless, flatfaced ball
- Ball-Ended Thrust Screws, headless, with fine-pitch thread
- Ball-Ended Thrust Screws, headless, flatfaced ball and hexalobular socket

Drawing





Order information


d ₁	Dimensions I ₂ d ₃ Ball diameter			ws	Load capacity for static load ¹⁾ max.	ă	Art. No.
[mm]				[mm]	[kN]	[9]	
flat-faced ball, bearing surface plain, Stainless steel							
M16	35	10.7	12	8	36	38	22700.0844

¹⁾ Statements on load capacity are not valid for the stainless steel type.



www.halder.com Page 1 of 2
Published on: 10.8.2024

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 10.8.2024