Mounting Pads • protected against slipping 22590.1120



Product Description

Mounting pads can be used as foot or thrust pad. Not parallel bearing surfaces up to 15° degrees can be compensated.

The plastic cover on the mounting pad prevents slipping.

Material

Ball element

Stainless steel 1.4305

Rubber capRubber, black

Pad


• Thermoplastic POM, white


More information

Notes

For the versions $d_1 = M10$ and M12 the lock nut conforms to DIN 934.

Drawing





Order information

Dimensions d1 d2 h1 h2 t ~ ~ ~					ws	Load capacity for static load max.	ă.	Art. No.
[mm]					[mm]	[kN]	[g]	
pad from thermoplastic, ball element from stainless steel – picture 1, Thermoplastic								
M20	67	49.5	19.5	17	30	22	190	22590.1120

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.