# Seating Pins • pin shape 22680.0452




### **Product Description**

To be used as solid and precise seat and stop. The pin-shaped form of this seating pin allows an application in components with narrow seating points. Bearing surface induction hardened and grounded.

#### **Material**

· Heat-treated steel, tempered, blackened

## Drawing




picture 1


picture 2


## **Order information**

Dimensions						WS	Tightening torque	Ĩ	Art. No.
l₁ ±0.01	d <sub>1</sub>	d <sub>2</sub>	I <sub>3</sub>	t	d <sub>3</sub>		max.	-	
[mm]						[mm]	[Nm]	[g]	
with female thread – picture 2									
with female t	hread – pictur	re 2							

### **Application example**







#### Compliance

#### **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.