

Ball-Ended Thrust Screws • headless, flat-faced ball
22720.0608



Product Description

Ball-ended thrust screws with thermoplastic ball are used for pressure sensitive pieces. Ball-ended thrust screws can also be used for clamping, tightening or supporting of non-parallel surfaces. The flat-faced, movable ball enables a flat load transmission.

Material

- Ball**
- Ball-bearing steel, hardened
- Screw**
- Heat-treated steel, 1200 ±100 N/mm²


More information

Notes

Ball not secured against rotating.
Special types on request.

- References**
- Thread lock on request, please refer to appendix - Technical Data -
- Further products**
- Ball-Ended Thrust Screws, headless, ball protected against rotating
 - Ball-Ended Thrust Screws, headless, with fine-pitch thread
 - Ball-Ended Thrust Screws, headless, short
 - Ball-Ended Thrust Screws, headless, flat-faced ball and hexalobular socket

Drawing




Order information

Dimensions				WS	Load capacity for static load ¹⁾	max.	[g]	Art. No.
d ₁	l ₂	d ₃ [mm]	Ball diameter	[mm]	max. [kN]	[°C]		
bearing surface plain , Heat-treated steel								
M10	40	6	7	5	20	250	18	22720.0608

¹⁾ Statements on load capacity are not valid for the stainless steel type (except the type fitted with thermoplastic balls).

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure
<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.