Ball-Ended Thrust Screws • headless, flat-faced ball 22720.0894



Product Description

Ball-ended thrust screws with thermoplastic ball are used for pressure sensitive pieces. Ball-ended thrust screws can also be used for clamping, tightening or supporting of non-parallel

The flat-faced, movable ball enables a flat load transmission.

Material

Ball

· Ball-bearing steel, hardened

Screw

Heat-treated steel, 1200 ±100 N/mm²

More information

Notes


Ball not secured against rotating. Customized design on request.

Thread lock on request, please refer to appendix - Technical Data -

Further products

- Ball-Ended Thrust Screws, headless, ball protected against rotating
- Ball-Ended Thrust Screws, headless, with fine-pitch thread
- Ball-Ended Thrust Screws, headless, short
- Ball-Ended Thrust Screws, headless, flatfaced ball and hexalobular socket

Drawing



Order information

d ₁	l ₂	Dimensions d ₃ [mm]	Ball diameter	WS	Load capacity for static load ¹⁾ max. [kN]	max.	[g]	Art. No.
bearing surface	ce ribbed, Heat-		5.5	4	15	250	5.1	22720.0894

¹⁾ Statements on load capacity are not valid for the stainless steel type (except the type fitted with thermoplastic balls).


Erwin Halder KG



www.halder.com Page 1 of 2

Published on: 13.11.2024

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 13.11.2024

Erwin Halder KG www.halder.com