# Stops · cylindrical 23280.0118



## **Product Description**

The T-slot guide enables a quick and precise location of the workpiece. The cylindrical form of the stop facilitates to determine the 0-point coordinate. The short form, which is ground to a height tolerance of  $\pm$  0,01 mm, can also be used for locating.

#### **Material**

#### Stop


• Steel, case-hardened, ground

# Holding plate

· Steel, blackened

• Steel, quality 8.8 (ISO 4762)

### **Drawing**



# **Order information**


T-slot size	Dimensions						Screw	I I	Art. No.
	l <sub>1</sub>	а	b	d	h	l <sub>2</sub>	ISO 4762	_	
	±0.01	-0.6	h6	±0.01					
[mm]	[mm]						[mm]	[g]	
18	25	18	18	40	10	15	M10 x 50	367	23280.0118



www.halder.com Page 1 of 2 Published on: 10.8.2024

Erwin Halder KG

### **Application example**



#### Compliance

### **RoHS** compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

### Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

#### **Contains Proposition 65 substances**



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

Page 2 of 2 Published on: 10.8.2024