Down-Thrust Clamps • moveable, size 40

23310.0083



Product Description

The moveable down-thrust clamps are used, amongst other things, when swivel movements are not possible because of the workpiece.

The clamps have the following advantages:

- Easier and quicker workpiece change by moving the clamping claws forwards or backwards.
- The clamping range in horizontal direction is between I₁ min. and I₁ max..
- To change the workpiece, the clamping claw can be pushed back from $\mbox{\it l}_1$ max. by dimension $\mbox{\it l}_2.$
- Rapid manual clamping by means of the clamping screw, the adjustable clamping lever, or the double eccentric tension lever.
- As with all down-thrust clamps, the clamping claw of this version can also be swivelled away to the left or right. The use of positioning ring 23310.0350 allows the clamping position to be fixed. Here h₁ min. increases by at least 7 mm (stroke minus 7 mm).
- · Compact design, therefore less space requirement when clamping.
- Easily adjustable even to large clamping heights, using the height adjusting cylinders.

As the force applied by the operator is not known for the versions with levers, the clamping force is given in the tables as a guide value. The average value was determined by tests.

Material

Clamp

 Case-hardened steel, case-hardened, blackened and ground

Tension lever

 Zinc die-cast, plastic coated, orange similar to RAL 2004, matt structure

Assembly

Down-thrust clamps can be attached in two ways:

- 1. in a T-slot, using a nut for T-slots DIN 508 (EH 23010.)
- 2. with the set screw directly in the mounting plate of, for example, a fixture

The cylinder must make contact over the whole surface.

Operation

- 1. Push clamping claw backwards.
- 2. Insert workpiece.
- 3. Push clamping claw forwards.
- 4. Adjust clamping position of clamping claw using the knurled screw.
- 5. Secure / lock the clamping position using the knurled nut.

More information

References

The clamping height can be increased by using height adjusting cylinders EH 23310. and disks EH 1107. and EH 1108. It can be reduced by employing clamping inserts, e.g. EH 22730.

Further products

- · Positioning Rings, for down-thrust clamp
- Height Adjusting Cylinders
- Spacers
- Wrenches




Erwin Halder KG

www.halder.com Page 1 of 3

Published on: 10.8.2024

Drawing




Order information

d ₁										Stroke [mm]	Clamping force ¹⁾ [kN]	[9]	Art. No.
with adjustable clamping lever with axial bearing – picture 1													
40	30 13 M12	70 – 90 95 – 115	15	20	82	38 – 55	30	90 – 107	108	20	6	1400	23310.0083

¹⁾ Average value established in trials.

Page 2 of 3 Published on: 10.8.2024

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

www.halder.com



Page 3 of 3 Published on: 10.8.2024