# Floating Clamps • combined clamping and locking M 12

23320.0012



#### **Product Description**

The floating clamp is used to clamp and support additional clamping points on components. The benefits of the floating clamp are:

- Avoids vibration during the processing
- Clamps ribs, beads and shackles to reinforce clamped components
- Distortion-free clamping of raw parts.

#### Material

## Adjustable body

· Aluminium, red anodised

Case-hardened steel, nitrided, manganese phosphated and ground

#### Clamping jaws

Case-hardened steel, nitrided, manganese phosphated

## **Assembly**

- 1. Mount the floating clamp (M 12 connection thread) onto the device with a wrench (WS 46).
- 2. Adjust the height limit stop and the rotating area with the red sleeve and clamp with a set screw (3 x WS 2.5). When setting the height limit, consider tolerance of workpiece.

#### **Operation**

- 1. Push the floating clamp downwards.
- 2. Pivot the clamping jaws in as far as possible. The floating clamp contacts the bottom of the workpiece with a slight spring load
- 3. Tighten the floating clamp with a hexagonal nut (WS 18) having a min. torque of 15 Nm and a maximum torque of 30 Nm. In the clamping process, the workpiece is clamped and simultaneously supported.
- 4. Releasing is done in reverse order.

#### More information

#### **Notes**

The thread bore must always be closed for safe functioning, e.g. set screw M 12 x 10. For specific clamping situations, the standard clamping jaws supplied can be exchanged or replaced (see catalogue drawing: screw ISO 4762 - M8 - 12.9, M max. = 43 Nm).

Additional flexible possibility of fitting with holder 23470.0250 or holding plate for downhold clamps 23210.0740.

## **Accessories**

As an accessory, we offer clamping jaws with an increased clamping range, refer to 23320.0050-.0058, as well as pivot jaws, refer to 23320.0148-.0156.

## **Further products**

- Holding Plates, for down-hold clamps
- Floating Clamps, separate clamping and locking M 12
- Standard Clamping Jaws, for floating clamp
- · Clamping Jaws, for floating clamp M 12




Erwin Halder KG

www.halder.com

Page 1 of 4 Published on: 10.8.2024

## **Drawing**




## **Order information**

i i	Art. No.
[9]	
2103	23320.0012

## **Application example**



www.halder.com Page 2 of 4
Published on: 10.8.2024



## Compliance

## **RoHS** compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

## Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

## **Contains Proposition 65 substances**



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 4 of 4
Published on: 10.8.2024