

**Ball Lock Pins · self-locking, with standard handle, titanium**  
EH 22390.



**Product Description**

Ball lock pins made from titanium stand out due to the following positive material features:

- Over 40% lighter weight compared to a steel variant
- Absolutely corrosion resistant.

The version made from titanium is used in areas such as lightweight construction, maritime environments and chemical manufacturing.

For quick fastening, locking, adjusting, changing and securing. Quickly and easily unlockable for frequently repeated connections.

Compact design with standard handle.

**Material**

**Pin part**

- Titanium

**Ball**

- Ceramic

**Spring**

- Corrosion resistant alloy

**Operation**

The balls are unlocked by pressing the button.

**More information**

**Notes**

Customized design on request.


**Accessories**

Can easily be fitted with retaining cable  
EH 22400.

**Further products**

- Ball Lock Pins, self-locking, with standard handle
- Retaining Cables

**Drawing**




**Order information**

d <sub>1</sub>		l <sub>1</sub>		Dimensions		Location hole H11	Shearing resistance, two-shear <sup>1)</sup> min.	max.	g	Art. No.
-0.04	-0.08	+0.6		d <sub>2</sub>	d <sub>3</sub>					
				[mm]		[mm]	[kN]	[°C]	[g]	
6	10	7.0	10	7.0	26.2	6	23	400	6.6	<a href="#">22390.0022</a>
6	20	7.0	10	7.0	26.2	6	23	400	7.7	<a href="#">22390.0024</a>
6	30	7.0	10	7.0	26.2	6	23	400	8.8	<a href="#">22390.0026</a>
6	40	7.0	10	7.0	26.2	6	23	400	9.9	<a href="#">22390.0028</a>
6	50	7.0	10	7.0	26.2	6	23	400	11.0	<a href="#">22390.0030</a>
8	20	9.5	14	8.2	33.1	8	43	400	18.0	<a href="#">22390.0034</a>
8	30	9.5	14	8.2	33.1	8	43	400	20.0	<a href="#">22390.0036</a>
8	40	9.5	14	8.2	33.1	8	43	400	23.0	<a href="#">22390.0038</a>
8	50	9.5	14	8.2	33.1	8	43	400	25.0	<a href="#">22390.0040</a>
10	20	12.0	14	9.6	33.1	10	43	400	22.0	<a href="#">22390.0044</a>
10	30	12.0	14	9.6	26.2	10	69	400	25.0	<a href="#">22390.0046</a>
10	40	12.0	14	9.6	26.2	10	69	400	29.0	<a href="#">22390.0048</a>
10	50	12.0	14	9.6	26.2	10	69	400	32.0	<a href="#">22390.0050</a>
10	60	12.0	14	9.6	26.2	10	69	400	35.0	<a href="#">22390.0052</a>

<sup>1)</sup> Shearing resistance similar to DIN 50141 (determined by tests)

Application example



## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.