Locating Bushings • for lifting pins 22350.0912



Product Description

Locating bushings are used for quick and safe locating of lifting pins EH 22350 / EH 22351. Corrosion and abrasion resistant.


Material


 Stainless steel 1.4542, precipitationhardened

Assembly

Safe tolerances and consistent function. Easily incorporated into different materials Can be mounted in blind holes. For thin-walled parts, lock nuts are used for assembly.

Drawing








Order information

Dimensions		For nominal	Dimensions				WS	Tightening	x	Loa	id capa	city	For lifting pin		Art. No.
d ₁	d ₂	length	d ₃	d4	l ₁	l ₂		torque		F1	F2	F ₃			
H11			-0.2	+0.3				max.							
[mm]		[mm]	[mm]			[mm]	[Nm]	[mm]		[kN]			[g]		
10	M20 x 1,5	25	28	12.2	35.5	24	24	145	1.5	2.7	2.4	2.1	22350.0623 / .0723	74	22350.0912

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.