# **Ball-Ended Thrust Screws** • headless, ball protected against rotating 22700.0806



## **Product Description**

Ball-ended thrust screws can also be used for clamping, tightening or supporting of non-parallel surfaces.

The flat-faced, movable ball enables a flat load transmission.

# Material

- Ball
- · Stainless steel, hardened

Screw

Stainless steel 1.4305

#### More information

#### Notes

Ball protected against rotating. Special types on request.


#### References

Thread lock on request, please refer to appendix - Technical Data -

#### **Further products**

- Ball-Ended Thrust Screws, headless, flatfaced ball
- Ball-Ended Thrust Screws, headless, with fine-pitch thread
- Ball-Ended Thrust Screws, headless, flatfaced ball and hexalobular socket

#### Drawing




## **Order information**

Dimensions				ws	Load capacity	Ĭ	Art. No.
d <sub>1</sub>	I <sub>2</sub>	d <sub>3</sub>	Ball diameter		for static load <sup>1)</sup> max.		
	l	[mm]		[mm]	[kN]	[9]	
flat-faced ball, bearing surface plain, Stainless steel							
M6	25	3.2	4	3	6	3.8	22700.0806

<sup>1)</sup> Statements on load capacity are not valid for the stainless steel type.

# **Application example**



# Compliance

### **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

## **Does not contain Proposition 65 substances**

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.