Spring Plungers • smooth, with collar and pin 22080.0108



Product Description

To be used for locating, tightening, as an assembly support, for applying pressure, as a detent, for ejection or as a shock absorber.

Material

Pin

· Stainless steel 1.4305

Body

· Stainless steel 1.4303

Spring

Stainless steel

Assembly


A tolerance of H7 is recommended for the locating hole of d₁.

More information

Notes

Special types on request.
Spring plungers are specially tested for spring range and forces.

Drawing





Order information


Dimensions									Stroke	Spring load ¹⁾			Location hole	I	Art. No.
d ₁	d ₂	d ₃	d ₄	d ₅	I ₁	l ₂	l ₃	l ₄	S	F ₁	F ₂	max.	H7		
+0.1				±0.04		~	~	~		~	~				
[mm]								[mm]		[N]	[°C]	[mm]	[g]		
body	body and pin from stainless steel														
8	6.2	8.5	7.55	8	18	1.1	2.9	9.5	6.5	9	20.1	250	8	4	22080.0108

¹⁾ statistical average value

Application example







Erwin Halder KG

www.halder.com Page 1 of 2

Published on: 10.8.2024

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 10.8.2024