# Threaded Lifting Pins • self-locking, with rotatable shackle





## **Product Description**

Heavy-duty lifting element for quick and easy use, with moveable, rotatable shackle and locking stud to provide protection against unintentional unlocking. For lifting loads, the threaded lifting pin is inserted into a threaded hole. In contrast to a ringbolt, time-consuming screwing in and out is therefore unnecessary. The rotatable shackle will always align with the tensile direction of pull without the pin rotating. This prevents the lifting device from being turned out of the thread and the component can be lifted safely.

All versions are corrosion-protected. The version made of stainless steel is also resistant to corrosion and weathering, so it is also suitable for external use. In addition, the high-strength, precipitation-hardened pin makes extreme loads possible.

#### Material

#### Pin part

· Stainless steel 1.4542, precipitationhardened

#### Press button

Aluminium, orange, anodised

#### Threaded element

· Stainless steel 1.4542, precipitationhardened

#### **Shackle**

· Stainless steel 1.4571

#### Spring

Stainless Steel

## **Assembly**

Threaded lifting pins can be mounted into a thread that is true to gauge.

#### Mounting:

- 1. Press in the button and hold it down.
- 2. Insert the threaded lifting pin.
- 3. Release the button (The button must be back in its original position.).
- 4. Tighten the threaded lifting pin by hand, until it bears compleately on the bearing surface.
- 5. It must be ensured that the threaded segments are engaged in the mounting thread.

#### Dismantling:

- 1. Unscrew the threaded lifting pin approx. a quarter of a turn anticlockwise.
- 2. Press in the button and hold it down.
- 3. Remove the threaded lifting pin.
- 4. Release the button.

## **Operation**

Each threaded lifting pin contains an instruction manual with an EC Declaration of Conformity.

## More information

## **Further products**


- · Lifting Pins, self-locking
- Lifting Pins, self-locking, stainless steel
- Threaded Lifting Pins, self-locking
- Threaded Lifting Pins, self-locking, for centre holes according to DIN 332
- Threaded Lifting Pins, self-locking INCH
- Threaded Lifting Pins, self-locking, with rotatable shackle - INCH



Erwin Halder KG www.halder.com Published on: 10.8.2024

Page 1 of 8

# **Drawing**



## **Order information**

Dimensions	Load capacity	Locating thread	ß.	Tightenine torque	Ĭ	Art. No. <sup>1)</sup>
	according to			max.		
$\begin{array}{c c c c c c c c c c c c c c c c c c c $	DIN EN 13155   F <sub>1</sub>   F <sub>2</sub>   F <sub>3</sub>		max.			
[mm]	[kN]	[mm]	[°C]	[Nm]	[9]	
Stainless steel						
M24         27         20.7         35         59         50         36         42         79.2         55.6         70         102         173         59         22	18 11.1 8.6	M24	250	3	1984	22353.1024

 $<sup>^{1)}\,</sup> from \ 150^{\circ} C$  linear decrease of the load capacity by 23%

Page 2 of 8 Published on: 10.8.2024

# **Application example**






www.halder.com Page 3 of 8
Published on: 10.8.2024





www.halder.com Page 4 of 8
Published on: 10.8.2024





www.halder.com Page 5 of 8
Published on: 10.8.2024





www.halder.com Page 7 of 8
Published on: 10.8.2024

## Compliance

# RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

## Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

## **Contains Proposition 65 substances**



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

Page 8 of 8 Published on: 10.8.2024

www.halder.com