Ball-Ended Thrust Screws • headless, flat-faced ball 22720.0984



Product Description

Ball-ended thrust screws with thermoplastic ball are used for pressure sensitive pieces. Ball-ended thrust screws can also be used for clamping, tightening or supporting of non-parallel surfaces.

The flat-faced, movable ball enables a flat load transmission.

Material

Ball

• Ball-bearing steel, hardened

Screw

Heat-treated steel, 1200 ±100 N/mm²

More information

Notes

Ball not secured against rotating. Customized design on request.

References

Thread lock on request, please refer to appendix - Technical Data -

Further products

- Ball-Ended Thrust Screws, headless, ball protected against rotating
- Ball-Ended Thrust Screws, headless, with fine-pitch thread
- Ball-Ended Thrust Screws, headless, short
 Ball-Ended Thrust Screws, headless, flatfaced ball and hexalobular socket

Drawing



Order information

Dimensions					Load capacity	ß	Ĩ	Art. No.
d ₁	l ₂	d ₃	Ball diameter		for static load ¹⁾ max.	max.		
[mm]				[mm]	[kN]	[°C]	[g]	
bearing surface ribbed, Heat-treated steel								
M24	50	15.8	18	12	120	250	125	22720.0984

¹⁾ Statements on load capacity are not valid for the stainless steel type (except the type fitted with thermoplastic balls).

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.