$\textbf{Monitoring Units} \bullet \text{for positioning sensors, pneumatic}$

22800.0701



Product Description

The monitoring unit is used in combination with positioning sensors (EH 22800). Together with the positioning sensors, the backwash pressure sensor makes it possible to poll the correct workpiece positioning.

Material

Housing

plastic

More information

Notes

Further information on request.

((

22800.0702 PLC/CNC 22800.0701 22800.0711 22800.0714 22800.0711 22800.0713 22800.0715 22800.0715

Erwin Halder KG

Page 1 of 4 Published on: 10.8.2024

Order information

Working pressure	i	Art. No.			
[bar]	[g]				
backwash pressure sensor with LCD display, Ø 4 mm pneumatic hose connection, analogue and digital output signals					
0 – 10	162	22800.0701			



www.halder.com Page 2 of 4 Published on: 10.8.2024

Accessories

2000 - 84.0 22000.0702	Accessories							
Immail (a)		L	D	¥	Art. No.			
installation frame for backwash pressure sensor, for installation into a control panel (max. wall thickness 5 mm) 2000 — 44.0 22000.0702 installation frame for backwash pressure sensor, for installation into a control panel (max. wall thickness 5 mm) — — 26.0 22000.0703 plug-in-power supply, lapus 100-240 V AC / output 24 V DC 500 mA, with M12 plug socket — — 100.0 — 220.0 22000.0703 pressure regulator, max. input pressure 12 bar / output pressure 2 bar, 144* maile thread two-sided — — 22.0 2200.0704 pressure regulator, max input pressure 12 bar / output pressure 2 bar, 144* female thread on push-in connector (pneumatic hose 0.4 mm) — — 17.0 22000.0711 Trust-in connector, for pneumatic hose 0.4 mm — — 4.7 22000.0713 Trust-in connector for pneumatic hose 0.4 mm — — 7.6 22000.0714 Ervein Halder KG www.halder.com Papps 3 of 4 Papps		[mm]	[mm]	_				
installation frame for backwash pressure sensor, for installation into a control panel (max. wall thickness 5 mm) 26.0 22000.0703 plug-in power supply, input 100-240 V AC / output 24 V DC 500 mA, with M12 plug socket - 1500 - 100.0 22000.0704 pressure regulator, max. input pressure 12 bar / output pressure 2 bar, 1/4" male thread two-sided 22.0 22000.0710 connection piece for connecting pressure regulator and pneumatic hose, 1/4" female thread on push-in connector (pneumatic hose 9 4 mm) 17.0 22000.0711 pneumatic hose 9 4 mm - 4.7 22000.0713 T-push-in connector, for pneumatic hose 0.4 mm 4.7 22000.0713 T-push-in connector for pneumatic hose 0.4 mm 7.6 22000.0714 Erwin Halder KG www.halder.com Page 3 cf4	circular connector cable for connecting backwash pressure sensor to control / bus system, M12 connection on free cable end (4-pin)							
Piligal n power supply Input 100-240 V AC / output 24 V DC 500 mA, with M12 plug socket		2000	-	84.0	22800.0702			
plug-in power supply, input 100-240 V AC / output 24 V DC 500 mA, with M12 plug socket 1500 - 100.0 22800.0704 pressure regulator, max. input pressure 12 bar / output pressure 2 bar, 1/4" male thread two-sided - 22.0 22800.0710 connection piece for connecting pressure regulator and pneumatic hose, 1/4" female thread on push-in connector (pneumatic hose Ø 4 mm) - 17.0 22800.0711 pressure regulator and pneumatic hose, 1/4" female thread on push-in connector (pneumatic hose Ø 4 mm) - 17.0 22800.0712 push-in connector, for pneumatic hose Ø 4 mm - 4.7 22800.0713 T-push-in connector for pneumatic hose Ø 4 mm - 7.6 22800.0714	installation frame for back	wash pressure sensor, for installation into	a control panel (max. v	vall thickness 5 mm)				
pressure regulator, max. input pressure 12 bar / output pressure 2 bar, 1/4" male thread two-sided - 22.0 22890.0710 connection piece for connecting pressure regulator and pneumatic hose, 1/4" female thread on push-in connector (pneumatic hose Ø 4 mm) - 17.0 22890.0711 pressure regulator and pneumatic hose, 1/4" female thread on push-in connector (pneumatic hose Ø 4 mm) - 17.0 22890.0711 push-in connector, for pneumatic hose Ø 4 mm - 4.7 22890.0713 T-push-in connector for pneumatic hose Ø 4 mm - 7.6 22890.0714		-	-	26.0	22800.0703			
pressure regulator, max. input pressure 12 bar / output pressure 2 bar, 1/4" male thread two-sided 22.0 22800.0710 connection piece for connecting pressure regulator and pneumatic hose, 1/4" female thread on push-in connector (pneumatic hose Ø 4 mm) 17.0 22800.0711 pneumatic hose Ø 4 mm 4.7 22800.0712 push-in connector, for pneumatic hose Ø 4 mm 4.7 22800.0713 T-push-in connector for pneumatic hose Ø 4 mm 7.6 22800.0714	plug-in power supply, inpu	it 100-240 V AC / output 24 V DC 500 mA, w	ith M12 plug socket					
22.0 22800.0710 connection piece for connecting pressure regulator and pneumatic hose, 1/4" female thread on push-in connector (pneumatic hose Ø 4 mm) 17.0 22800.0711 pneumatic hose Ø 4 mm 5000 4 43.0 22800.0712 push-in connector, for pneumatic hose Ø 4 mm 4.7 22800.0713 T-push-in connector for pneumatic hose Ø 4 mm 7.6 22800.0714 Erwin Halder KG www.halder.com Page 3 of 4			-		22800.0704			
connection piece for connecting pressure regulator and pneumatic hose, 1/4" female thread on push-in connector (pneumatic hose Ø 4 mm) 17.0 22800.0711 pneumatic hose Ø 4 mm 5000 4 43.0 22800.0712 push-in connector, for pneumatic hose Ø 4 mm 4.7 22800.0713 T-push-in connector for pneumatic hose Ø 4 mm 7.6 22800.0714 Erwin Halder KG www.halder.com Page 3 of 4	pressure regulator, max. in	nput pressure 12 bar / output pressure 2 ba	r, 1/4" male thread two	-sided				
		-	-	22.0	22800.0710			
pneumatic hose Ø 4 mm 5000 4 43.0 22800.0712 push-in connector, for pneumatic hose Ø 4 mm 4.7 22800.0713 T-push-in connector for pneumatic hose Ø 4 mm 7.6 22800.0714 Erwin Halder KG www.halder.com Page 3 of 4	connection piece for conne	onnection piece for connecting pressure regulator and pneumatic hose, 1/4" female thread on push-in connector (pneumatic hose Ø 4 mm)						
5000 4 43.0 22800.0712 push-in connector, for pneumatic hose Ø 4 mm 4.7 22800.0713 T-push-in connector for pneumatic hose Ø 4 mm 7.6 22800.0714 Erwin Halder KG www.halder.com Page 3 of 4		-	-	17.0	22800.0711			
push-in connector, for pneumatic hose Ø 4 mm 4.7 22800.0713 T-push-in connector for pneumatic hose Ø 4 mm 7.6 22800.0714 Erwin Halder KG www.halder.com Page 3 of 4	pneumatic hose Ø 4 mm							
4.7 22800.0713 T-push-in connector for pneumatic hose Ø 4 mm 7.6 22800.0714 Erwin Halder KG www.halder.com Page 3 of 4			4	43.0	22800.0712			
T-push-in connector for pneumatic hose Ø 4 mm - 7.6 22800.0714 Erwin Halder KG www.halder.com Page 3 of 4	push-in connector, for pne	ush-in connector, for pneumatic hose Ø 4 mm						
7.6 22800.0714 Erwin Halder KG www.halder.com Page 3 of 4		-	-	4.7	22800.0713			
Erwin Halder KG www.halder.com Page 3 of 4	r-push-in connector for pneumatic hose Ø 4 mm							
		-	-	7.6	22800.0714			
Y-push-in connector for pneumatic hose Ø 4 mm			www	.halder.com	Page 3 of 4			
	Y-push-in connector for pneumatic hose Ø 4 mm							

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 4 of 4 Published on: 10.8.2024

www.halder.com