# Swing Bolts • DIN 444, form B

22980.0222



# **Product Description**

Swing bolts similar to DIN 444 however, steel design with higher quality 8.8. The stainless steel A2-50 design has a tensile strength of min. 500 N/mm<sup>2</sup>.

#### Material

Heat-treated steel, tempered, quality 8.8, black

### More information

#### **Notes**

Special types on request.


#### References


For torques please refer to appendix - Technical Data -

#### **Further products**

• Swing Bolts, DIN 444, form B, quality 8.8 high precision design

## **Drawing**





### **Order information**

Dimensions						I I	Art. No.
d <sub>1</sub>	I	<b>d<sub>2</sub></b> H9	$d_3$	b	s	_	
[mm]						[g]	
Heat-treated steel							
ricat-treated Steer							

# Compliance

## **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Erwin Halder KG

### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 1 of 1
Published on: 10.8.2024