Swing Bolts • DIN 444, form B

22980.0278



Product Description

Swing bolts similar to DIN 444 however, steel design with higher quality 8.8. The stainless steel A2-50 design has a tensile strength of min. 500 N/mm².

Material

· Heat-treated steel, tempered, quality 8.8, black

More information

Notes

Special types on request.


References


For torques please refer to appendix -Technical Data -

Further products

• Swing Bolts, DIN 444, form B, quality 8.8 high precision design

Drawing





Order information

Dimensions						-	Art. No.
d ₁	l	d₂ H9	d ₃	b	s	_	
[mm]						[g]	
Heat-treated steel							

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Erwin Halder KG

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 1 of 1 Published on: 10.8.2024