Down-Hold Clamps • without clamping lever, with support 23210.0551



Product Description

By tightening the ball-ended thrust screw the workpiece is simultaneously pressed towards the stops and fixture plate. The favourable leverage enables high horizontal clamping forces. When using T-Nuts EH 23010. / EH 23020. (DIN 508) they can also be applied to other slot sizes.

Material

• Steel, case-hardened, blackened, ground

More information


References

The integrated support is equipped with a locating thread to fit for example screwed rest buttons EH 22690., self-aligning pads EH 22730. / EH 22740.

Further products

- Nuts for T-Slots, DIN 508
- · Nuts for T-Slots, extended


Drawing



Order information

T-slot		Dimensions														Tightening	Ĩ	Art. No.
size	d1	d ₂	d ₃	b ₁	b ₂	h ₁	h ₂ ±0.01	h₃ ~	h₄ ~	I ₁	l ₂	I ₃	I ₄	S	force horizontal max.	torque max.		
[mm]	[mm]														[kN]	[Nm]	[g]	
with flat	vith flat clamping jaw – picture 1																	
10	M8	8.4	M8	32	12.1	44	15	40	28	52	28	72.5	38	3	7	3	566	23210.0551

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.