# **Ball Casters** • screwable, plain bearing 22752.0161



# **Product Description**

For positioning and aligning of workpieces.

Because of the slide bearing, the ball can roll permanently, and the surface of the workpiece is

At temperatures > 20°C, the carrying figure decreases linearly. (Example: at 90°C the load bearing capacity is max. 60%)

#### Material

## **Bearing**

· plastic

#### Ball

· Ball-bearing steel, hardened

#### Screw


· Free cutting steel, blackened

## More information

#### **Notes**

Special types on request.


## **Drawing**



# **Order information**

Dimensions			ws	Static carrying figure C <sub>0</sub>		<u></u>		I	Art. No.
d <sub>1</sub>	I <sub>1</sub>	Ball diameter			torque max.	min.	max.		
[mm]			[mm]	[N]	[Nm]	[°C]		[g]	
Free cutting steel									
M16	20	8.5	3	1986	3.21	-50	90	20	22752.0161

# **Application example**



Erwin Halder KG

www.halder.com Page 1 of 2

Published on: 10.8.2024

# Compliance

# **RoHS** compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

## Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

### **Contains Proposition 65 substances**



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 10.8.2024

Erwin Halder KG