# Tapered Shaft Hubs • without lock nut

# 25050.0008



# **Product Description**

By using tapered shaft hubs, all shaft-hub joints of machine elements such as sprocket wheels, gear wheels, belt pulleys, cams, levers etc. can be easily and efficiently established. It is a self-centering and non-floating tapered shaft hub in corrosion-protected design with a hexagon nut.

The rotational accuracy of the tapered shaft hubs is 0,03 mm.

#### Material

### **External part**

• Steel, zinc-plated by galvanization

#### Inner part

· Steel, nickel-plated

#### Nut


· Steel, nickel-plated

### More information

#### References

Comply with mounting instructions, mounting examples, and technical data.

# **Drawing**



Erwin Halder KG

#### **Order information**

| D  | Dimensions     |                | ws             | Tightening | Transferable torque | Transferable | Surface        | Surface              | Hub      | Shaft          | I        | Art. No. |            |
|----|----------------|----------------|----------------|------------|---------------------|--------------|----------------|----------------------|----------|----------------|----------|----------|------------|
| d₁ | d <sub>2</sub> | I <sub>1</sub> | l <sub>2</sub> |            | torque of the nut   | M            | axial load     | pressure             | pressure | bore           | diameter |          |            |
|    | _              |                |                |            | T <sub>A</sub>      | max.         | F <sub>a</sub> | of shaft             | of hub   | D <sub>1</sub> | $D_2$    |          |            |
|    |                |                |                |            | max.                |              | max.           | p <sub>W</sub>       | $p_N$    | H9             | h9       |          |            |
|    |                |                |                |            |                     |              |                | max.                 | max.     |                |          |          |            |
|    | [mm]           |                | [mm]           | [Nm]       | [Nm]                | [kN]         | [N/mm²]        | [N/mm <sup>2</sup> ] | [mm]     | [mm]           | [g]      |          |            |
| 8  | 16             | 22             | 17             | 16         | 16.9                | 23.4         | 5.8            | 179                  | 91       | 16             | 8        | 24       | 25050.0008 |


### **Accessories**

|                     | ws<br>[mm] | <b>[</b> 9] | Art. No.   |  |  |  |  |  |  |  |
|---------------------|------------|-------------|------------|--|--|--|--|--|--|--|
| special fork wrench |            |             |            |  |  |  |  |  |  |  |
|                     | 16         | 72          | 25050.0816 |  |  |  |  |  |  |  |



Page 1 of 2 Published on: 10.8.2024

# **Application example**



# Compliance

### **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

# Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Erwin Halder KG

# **Does not contain Proposition 65 substances**

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

# **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 10.8.2024