# Fixture Nuts • DIN 6330 (height 1,5 d) 23070.0120



# **Product Description**

Fixture nuts according to DIN 6330 have a spherical surface to match conical seats DIN 6319 (EH 23050.).

With this combination of fixture nut and conical seat, non-parallel clamping surfaces can be compensated.

#### **Material**


· Stainless steel 1.4305

#### More information

#### References

For torques and strengths please refer to appendix - Technical Data -

# **Drawing**




### **Order information**

Dimensions						I	Art. No. <sup>1)</sup>
d <sub>1</sub>	d <sub>2</sub>	е	m	r	s		
[mm]						[g]	
with lateral spherical bearing surface, form B, Stainless steel							
M20	22	34.6	30	27	30	110	23070.0120

<sup>1)</sup> DIN standard do not include these material.

# **Application example**



www.halder.com Page 1 of 2 Published on: 10.8.2024

# Compliance

# **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024

Erwin Halder KG www.halder.com