# Adjustable Clamping Levers • inner parts from stainless steel, with screw



## **Product Description**

Adjustable clamping levers with rust-proof inner parts. Suitable for multiple applications, e.g. medical environments, chemical industry, and so on.

## **Material**

#### Lever

 Zinc die-cast, plastic coated, orange similar to RAL 2004, matt structure

### Inner parts

· Stainless steel 1.4305

### Screw

· Stainless steel 1.4305

## **Operation**


By lifting the lever the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

### More information

## Notes

The screw part can be exchanged.

## **Drawing**




# Order information

Dimensions									I	Art. No.
d <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>	$d_3$	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	l <sub>2</sub>		
	[mm]								[g]	
orange										
13	M4	16	10	24.5	4	3.5	30.5	30	30	24390.0014



www.halder.com Page 1 of 2
Published on: 10.8.2024

# **Application example**



# Compliance

# **RoHS** compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

## Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

## **Contains Proposition 65 substances**



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

## **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024

www.halder.com