# **Adjustable Tension Levers**

# 24440.0318



## **Product Description**

#### **Material**

#### Lever

· Steel, blackened

#### Inner parts

• Steel, blackened, quality 5.8

#### Screw

· Steel, blackened, quality 5.8

#### Ball knob

• Thermosetting plastic PF 31, black, DIN 319

### **Operation**


**By lifting the lever** the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.


#### More information


#### **Notes**

The threaded portion can be exchanged.

#### **Drawing**







#### **Order information**

d <sub>1</sub>	d <sub>2</sub>	I <sub>1</sub>	d <sub>3</sub>	Dimensions $d_4  \left   d_5  \right   h_1  \left   h_2  \right   h_3  \left   I \right $ [mm]						<b>[</b> g]	Art. No.
with screw	/ – picture 2, S M12	teel 16	19	12	30	48.5	4.5	4.5	110	277	24440.0318

#### Compliance

#### **RoHS** compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

### Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

# **Contains Proposition 65 substances**



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Erwin Halder KG

### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 1 of 1
Published on: 10.8.2024