Height-Adjusting Elements 25120.0014



Product Description


For levelling of machines and installations.


For vertical adjustment, the self-locking height-adjusting elements are fitted with a fine-pitch thread. All elements have a throughgoing bore for fastening purposes. A turn-out lock serves as height limit for the maximum adjustment height.

Material

 Heat-treated steel, zinc-plated by galvanization, chromalized

Drawing






Order information


Dimensions					Stroke	For screw	Load capacity	Load capacity ¹⁾	Ĩ	Art. No.
d ₁	d ₂	d ₃	I ₁ ~	₂ ~	I₃ ~		for static load max.	max.		
[mm]				[mm]	[mm]	[kN]	[kN]	[g]		
9	32	M20 x 1	18	23	5	M8	65	48	86	25120.0014

¹⁾ Load capacity after deduction of the maximum preload force for screws 8.8.

Accessories

sickle spanner for vertica	For height adjusting element size d ₂ [mm] al adjustment	Dimensions of sickle spanner DIN 1810, form A [mm]	a	Art. No.
	32	30 – 32	46	25120.0982





Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.