Height-Adjusting Elements • orienting

25120.0214




Product Description

For levelling of machines and installations when bearing surfaces are not parallel. For vertical adjustment, the self-locking height-adjusting elements are fitted with a fine-pitch thread. All elements have a throughgoing bore for fastening purposes. A turn-out lock serves as height limit for the maximum adjustment height.

Material

Heat-treated steel, zinc-plated by galvanization, chromalized

Drawing



Order information

Dimensions					Stroke	For screw	Load capacity	Load capacity ¹⁾	I	Art. No.
d ₁	d ₂	d ₃	I ₁	l ₂	l ₃		for static load	max.		
			~	~	~		max.			
[mm]				[mm]	[mm]	[kN]	[kN]	[g]		
9	32	M20 x 1	26	31	5	M8	65	48	124	25120.0214

¹⁾ Load capacity after deduction of the maximum preload force for screws 8.8.


Accessories

	For height adjusting element size d ₂	Dimensions of sickle spanner DIN 1810, form A	i	Art. No.
	[mm]	[mm]	[g]	
sickle spanner for vertical	al adjustment			
3	32	30 – 32	46	25120.0982



www.halder.com Page 1 of 3
Published on: 10.8.2024

Application example





www.halder.com Page 2 of 3
Published on: 10.8.2024

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 3 of 3 Published on: 10.8.2024

www.halder.com

Erwin Halder KG