# Adjustable Clamping Levers • with female thread EH 24400.



## **Product Description**

Adjustable clamping levers find versatile applications when the area of use is confined or a specific lever position is required.

## Material

## Lever

- Zinc die-cast, plastic coated, orange similar to RAL 2004, matt structure
- Zinc die-cast, plastic coated, silver, similar to RAL 9006, matt structure
- Zinc die-cast, plastic coated, black, similar to RAL 9005, matt structure

## Threaded part

• Steel, blackened, quality 5

# Inner parts

Steel, blackened, quality 5.8


## Operation

**By lifting the lever** the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

#### More information

## Notes

The threaded portion can be exchanged.




# **Order information**

		Dimensions								Art. No.
d <sub>1</sub>	d2	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h4	l <sub>2</sub>	t ≥	-	
	[mm]									
orange										
13	М 3	10.0	24.5	4.0	3.5	30.5	30	7	26	24400.0032
13	M 4	10.0	24.5	4.0	3.5	30.5	30	9	25	24400.003
14	M 5	10.0	24.5	4.0	3.0	35.0	45	8	33	24400.011
14	M 6	10.0	24.5	4.0	3.0	35.0	45	8	33	24400.012
18	M 6	13.5	31.0	6.5	3.0	45.0	62	10	67	24400.031
18	M 8	13.5	31.0	6.5	3.0	45.0	62	10	71	24400.032
22	M 8	16.0	36.0	8.0	3.5	52.0	74	14	112	24400.041
22	M10	16.0	36.0	8.0	3.5	52.0	74	14	109	24400.042
25	M10	19.0	43.0	11.0	4.0	63.0	89	17	176	24400.051
25	M12	19.0	43.0	11.0	4.0	63.0	89	17	171	24400.052
30	M12	23.0	50.5	12.0	5.0	76.0	108	22	286	24400.061
30	M16	23.0	50.5	12.0	5.0	76.0	108	22	269	24400.062
ilver										
14	M 5	10.0	24.5	4.0	3.0	35.0	45	8	33	24400.011
14	M 6	10.0	24.5	4.0	3.0	35.0	45	8	33	24400.012
18	M 6	13.5	31.0	6.5	3.0	45.0	62	10	67	24400.031
18	M 8	13.5	31.0	6.5	3.0	45.0	62	10	71	24400.032
22	M 8	16.0	36.0	8.0	3.5	52.0	74	14	112	24400.0413

Dimensions								Ĩ	Art. No.	
d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h4	I <sub>2</sub>	t	-	
								2		
[mm]								[9]		
22	M10	16.0	36.0	8.0	3.5	52.0	74	14	109	24400.0423
25	M10	19.0	43.0	11.0	4.0	63.0	89	17	176	24400.0513
25	M12	19.0	43.0	11.0	4.0	63.0	89	17	171	24400.0523
30	M12	23.0	50.5	12.0	5.0	76.0	108	22	286	24400.0613
30	M16	23.0	50.5	12.0	5.0	76.0	108	22	269	24400.0623
black										
13	M 3	10.0	24.5	4.0	3.5	30.5	30	7	26	24400.0034
13	M 4	10.0	24.5	4.0	3.5	30.5	30	9	25	24400.0038
14	M 5	10.0	24.5	4.0	3.0	35.0	45	8	33	24400.0114
14	M 6	10.0	24.5	4.0	3.0	35.0	45	8	33	24400.0124
18	M 6	13.5	31.0	6.5	3.0	45.0	62	10	67	24400.0314
18	M 8	13.5	31.0	6.5	3.0	45.0	62	10	71	24400.0324
22	M 8	16.0	36.0	8.0	3.5	52.0	74	14	112	24400.0414
22	M10	16.0	36.0	8.0	3.5	52.0	74	14	109	24400.0424
25	M10	19.0	43.0	11.0	4.0	63.0	89	17	176	24400.0514
25	M12	19.0	43.0	11.0	4.0	63.0	89	17	171	24400.0524
30	M12	23.0	50.5	12.0	5.0	76.0	108	22	286	24400.0614
30	M16	23.0	50.5	12.0	5.0	76.0	108	22	269	24400.0624

# **Application example**



# Compliance

RoHS compliant Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

**Contains Proposition 65 substances** 



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

# Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

