Spring Plungers • with ball and slot - INCH 2B050.0370



Product Description

To be used for positioning, indexing, locking, latching as well as for other similar pressure applications.

Spring plungers can be used for locating or for applying pressure, as a detent or for ejection.

Material

Body

• Stainless steel 1.4305 (ASTM-A-582)

Ball

· Stainless steel, hardened

Spring

Stainless steel





More information

Characteristic

Notes

Special types on request.

Spring plungers are specially tested for spring range and forces.

· This product is manufactured in INCH dimensions.

References


A conversion table can be found in the technical data following these product information pages.

Thread lock: polyamide spot coating (for details please refer to the technical appendix). Calculation of indexing resistance, please refer to appendix - Technical Data -

Further products

- · Spring Plungers, with ball and slot
- · Locators, with bore hole, for spring plungers
- · Locators, smooth, for spring plungers


Drawing



Order information

Dimensions					Stroke	troke Spring load ¹⁾				Ĭ	Art. No.
d ₁		Thread	d2	I	S	F ₁	F₂ ∼	min.	max.		
	[in]		[in]		[in]	[]	b]	[°F]		[oz]	
stainless steel, heavy spring load, With thread lock											
#10-32	0.19	2A-UNF	3/32	33/64	0.025	3.3	4.8	-22	194	0.049	2B050.0370

1) statistical average value



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.