

## Cerniere • esecuzione lunga su un lato

### EH 25165.



#### Descrizione prodotto

The different versions cover many applications that require a low load.

These metal hinges are characterised by their simple design and the different versions:

- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

#### Materiale



##### Corpo

- Acciaio inox 1.4301
- Acciaio, zincato e passivato


##### Asse

- Acciaio inox 1.4301

#### Disegno



## Caratteristiche

b <sub>1</sub>	l <sub>1</sub>	b <sub>2</sub>	b <sub>3</sub>	Dimensioni						Forza di ritegno				Codice
				d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	F <sub>1</sub>	F <sub>2</sub>	F <sub>3</sub>		
[mm]										[N]			[g]	
<b>without bores – Fig. 1, acciaio inox</b>														
45	30	–	–	–	3	–	6	1,5	–	700	500	450	20	<a href="#">25165.0035</a>
60	40	–	–	–	4	–	8	2,0	–	1200	1000	1000	47	<a href="#">25165.0055</a>
75	50	–	–	–	6	–	10	2,0	–	1600	2000	1000	81	<a href="#">25165.0070</a>
90	60	–	–	–	6	–	10	2,0	–	1100	2500	1000	111	<a href="#">25165.0080</a>
<b>with bores – Fig. 2, acciaio inox</b>														
45	30	24,0	9,0	3,2	3	–	6	1,5	18	700	500	450	19	<a href="#">25165.0135</a>
60	40	32,5	12,5	4,2	4	–	8	2,0	18	1200	1000	1000	45	<a href="#">25165.0155</a>
75	50	40,0	15,0	5,2	6	–	10	2,0	30	1600	2000	1000	79	<a href="#">25165.0170</a>
90	60	48,0	18,0	5,2	6	–	10	2,0	36	1100	2500	1000	108	<a href="#">25165.0180</a>
<b>with bores – Fig. 2, Acciaio</b>														
45	30	24,0	9,0	3,2	3	–	6	1,5	18	700	500	450	19	<a href="#">25165.1035</a>
60	40	32,5	12,5	4,2	4	–	8	2,0	25	1200	1000	1000	45	<a href="#">25165.1055</a>
75	50	40,0	15,0	5,2	6	–	10	2,0	30	1600	2000	1000	79	<a href="#">25165.1070</a>
90	60	48,0	18,0	5,2	6	–	10	2,0	36	1100	2500	1000	108	<a href="#">25165.1080</a>
<b>with bores for countersunk screws – Fig. 3, acciaio inox</b>														
45	30	24,0	9,0	4,0	3	6,4	6	1,5	18	700	500	450	19	<a href="#">25165.0235</a>
60	40	32,5	12,5	5,0	4	8,3	8	2,0	25	1200	1000	1000	45	<a href="#">25165.0255</a>
75	50	40,0	15,0	5,0	6	8,3	10	2,0	30	1600	2000	1000	79	<a href="#">25165.0270</a>
90	60	48,0	18,0	5,0	6	8,3	10	2,0	36	1100	2500	1000	108	<a href="#">25165.0280</a>
<b>with bores for countersunk screws – Fig. 3, Acciaio</b>														
45	30	24,0	9,0	4,0	3	6,4	6	1,5	18	700	500	450	19	<a href="#">25165.2035</a>
60	40	32,5	12,5	5,0	4	8,3	8	2,0	25	1200	1000	1000	45	<a href="#">25165.2055</a>
75	50	40,0	15,0	5,0	6	8,3	10	2,0	30	1600	2000	1000	79	<a href="#">25165.2070</a>
90	60	48,0	18,0	5,0	6	8,3	10	2,0	36	1100	2500	1000	108	<a href="#">25165.2080</a>

## Conformità

### Conforme alla normativa RoHS

Conforme alla Direttiva 2011/65/UE e alla Direttiva 2015/863.

### Non contiene sostanze SVHC

Nessuna sostanza SVHC con più dello 0,1% p/p contenuto - elenco SVHC [REACH] aggiornato al 27.06.2024.

### Non contiene sostanze della Proposition 65

Nessuna sostanza contemplata nella Proposition 65

<https://www.P65Warnings.ca.gov/>

### Privo di minerali di conflitto

Questo prodotto non contiene sostanze designate come "minerali da conflitto" come tantalio, stagno, oro o tungsteno della Repubblica Democratica del Congo o dei paesi limitrofi.