

Cerniere
25165.0125



Descrizione prodotto

The different versions cover many applications that require a low load. These metal hinges are characterised by their simple design and the different versions:

- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

Materiale


Corpo

- Acciaio inox 1.4301


Asse

- Acciaio inox 1.4301

Disegno



picture 1 picture 2 picture 3



Caratteristiche

b ₁	l ₁	b ₂	Dimensioni					l ₂	Forza di ritegno			[g]	Codice
			d ₁	d ₂	h ₁	h ₂	F ₁		F ₂	F ₃			
			[mm]						[N]				
with bores – Fig. 2, acciaio inox													
40	40	25	4,2	4	8	2	25	2000	1000	1000	33	25165.0125	

Conformità

Conforme alla normativa RoHS

Conforme alla Direttiva 2011/65/UE e alla Direttiva 2015/863.

Non contiene sostanze SVHC

Nessuna sostanza SVHC con più dello 0,1% p/p contenuto - elenco SVHC [REACH] aggiornato al 23.01.2024.

Non contiene sostanze della Proposition 65

Nessuna sostanza contemplata nella Proposition 65

<https://www.P65Warnings.ca.gov/>

Privo di minerali di conflitto

Questo prodotto non contiene sostanze designate come "minerali da conflitto" come tantalio, stagno, oro o tungsteno della Repubblica Democratica del Congo o dei paesi limitrofi.