

## 高滾花螺母 · DIN 466

24780.0300



### 產品描述

Knurled nuts are very versatile. Three material versions for the different requirements

- Steel, blackened
  - Steel, zinc-plated by galvanization
  - Stainless steel
- are available.

Knurled nuts can be easily tightened and released by hand. The ribbed outer surface of the nut prevents slipping when tightening / releasing with the fingers. The high knurled nuts are manufactured according to DIN 467.

### 材質

- 不銹鋼 1.4305, 鈍化噴砂

### 更多資訊


#### 注意事項

根據 DIN 規範, 壓花的間距和深度也不同。


#### 更多產品

- 平壓花螺帽, DIN 467


### 圖面



### 訂單資訊

尺寸		尺寸				品號	
d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h	k			
		[mm]				[g]	
不銹鋼							
M10	36	20	23	8	85	24780.0300	

### 應用範例



## 遵守

### 符合 RoHS

符合指令 2011/65/EU 和指令 2015/863

### 不含 SVHC 物質

不含超過 0.1% w/w 的 SVHC 物質 - 截至 2024 年 6 月 27 日的 SVHC 清單。

### 不含 65 號提案物質

不包括 65 號提案物質

<https://www.P65Warnings.ca.gov/>

### 不含衝突礦物

本產品不含來自剛果民主共和國或鄰近國家的任何被指定為“衝突礦物”的物質，例如鈿、錫、金或鎳。