

위치 핀·볼타입 EH 22630.



제품 설명

볼타입 위치 핀은 가공물 삽입과 제거를 쉽게 해주고 클램핑을 잘못(사선으로) 하는 것을 방지함.

재질


- 공구강, 경화처리, 흑색처리와 연마처리
- 스테인레스 스틸 1.4305, 연마처리, 표면 열처리

더 많은 정보

추가 제품


- 위치 핀, DIN 6321
- 위치 핀, 홀이 있음 DIN 6321과 유사

그림




주문 정보

d ₁	d ₂	d ₃	d ₄	l ₁	l ₂	l ₃	t	r	b	위치 홀 D ₁ H7	제품 번호.	
g6	n6	-0,01 -0,05										
[mm]											[g]	
볼 타입 평평한 타입 - 그림 1, 공구강												
6	4	6	M2,5	4	6	2,0	4,5	1,0	-	4	1,8	22630.0306
8	6	8	M3	6	8	2,0	6,0	2,0	-	6	3,9	22630.0308
10	7	10	M3	7	10	2,5	6,0	2,5	-	7	6,7	22630.0310
12	8	12	M4	8	12	3,0	8,0	3,0	-	8	11,0	22630.0312
14	10	14	M4	10	14	3,5	8,0	3,5	-	10	20,0	22630.0314
16	12	16	M5	12	16	4,0	10,0	4,0	-	12	31,0	22630.0316
20	14	20	M5	14	20	5,0	10,0	5,0	-	14	58,0	22630.0320
22	16	22	M5	16	22	5,5	10,0	5,5	-	16	81,0	22630.0322
25	18	25	M5	18	25	6,0	10,0	6,0	-	18	118,0	22630.0325

d ₁ g6	d ₂ n6	d ₃ -0,01 -0,05	d ₄	l ₁	치수					위치 홀 D ₁ H7		제품 번호	
					l ₂	l ₃	t	r	b				
[mm]											[mm]	[g]	
볼 타입 평평한 타입 - 그림 1, 스테인리스 스틸													
6	4	6	M2,5	4	6	2,0	4,5	1,0	-	4	1,8	22630.0346	
8	6	8	M3	6	8	2,0	6,0	2,0	-	6	4,0	22630.0348	
10	7	10	M3	7	10	2,5	6,0	2,5	-	7	6,7	22630.0350	
12	8	12	M4	8	12	3,0	8,0	3,0	-	8	11,0	22630.0352	
14	10	14	M4	10	14	3,5	8,0	3,5	-	10	20,0	22630.0354	
16	12	16	M5	12	16	4,0	10,0	4,0	-	12	31,0	22630.0356	
20	14	20	M5	14	20	5,0	10,0	5,0	-	14	58,0	22630.0360	
볼 타입 납작한 타입 - 그림 2, 공구강													
6	4	6	M2,5	4	6	2,0	4,5	1,0	1,70	4	1,5	22630.0406	
8	6	8	M3	6	8	2,0	6,0	2,0	2,00	6	3,2	22630.0408	
10	7	10	M3	7	10	2,5	6,0	2,5	2,50	7	5,3	22630.0410	
12	8	12	M4	8	12	3,0	8,0	3,0	2,50	8	8,0	22630.0412	
14	10	14	M4	10	14	3,5	8,0	3,5	3,76	10	16,0	22630.0414	
16	12	16	M5	12	16	4,0	10,0	4,0	4,30	12	25,0	22630.0416	
20	14	20	M5	14	20	5,0	10,0	5,0	5,00	14	46,0	22630.0420	
22	16	22	M5	16	22	5,5	10,0	5,5	5,00	16	63,0	22630.0422	
25	18	25	M5	18	25	6,0	10,0	6,0	5,60	18	92,0	22630.0425	
볼 타입 납작한 타입 - 그림 2, 스테인리스 스틸													
6	4	6	M2,5	4	6	2,0	4,5	1,0	1,70	4	1,5	22630.0446	
8	6	8	M3	6	8	2,0	6,0	2,0	2,00	6	3,2	22630.0448	
10	7	10	M3	7	10	2,5	6,0	2,5	2,50	7	5,3	22630.0450	
12	8	12	M4	8	12	3,0	8,0	3,0	2,50	8	8,0	22630.0452	
14	10	14	M4	10	14	3,5	8,0	3,5	3,76	10	16,0	22630.0454	
16	12	16	M5	12	16	4,0	10,0	4,0	4,30	12	25,0	22630.0456	
20	14	20	M5	14	20	5,0	10,0	5,0	5,00	14	46,0	22630.0460	
편평한 볼, 단차 없음 - 그림 3, 공구강													
5	5	5	M2,5	6	5	2,0	4,5	1,0	-	5	2,4	22630.0505	
6	6	6	M3	8	6	2,0	5,0	1,0	-	6	2,9	22630.0506	
8	8	8	M3	10	8	2,0	6,0	2,0	-	8	6,0	22630.0508	
10	10	10	M3	13	10	2,5	6,0	2,5	-	10	12,0	22630.0510	
12	12	12	M4	15	12	3,0	8,0	3,0	-	12	21,0	22630.0512	
14	14	14	M4	17	14	3,5	8,0	3,5	-	14	34,0	22630.0514	
16	16	16	M5	20	16	4,0	10,0	4,0	-	16	51,0	22630.0516	
20	20	20	M5	25	20	5,0	10,0	5,0	-	20	101,0	22630.0520	
25	25	25	M5	25	25	6,0	10,0	6,0	-	25	176,0	22630.0525	
30	30	30	M6	30	30	8,0	12,0	8,0	-	30	307,0	22630.0530	
40	40	40	M6	40	40	10,0	12,0	10,0	-	40	729,0	22630.0540	
50	50	50	M6	50	50	12,0	12,0	12,0	-	50	1422,0	22630.0550	
편평한 볼, 단차 없음 - 그림 3, 스테인리스 스틸													
5	5	5	M2,5	6	5	2,0	4,5	1,0	-	5	1,8	22630.0565	
6	6	6	M3	8	6	2,0	5,0	1,0	-	6	3,4	22630.0566	
8	8	8	M3	10	8	2,0	6,0	2,0	-	8	6,0	22630.0568	
10	10	10	M3	13	10	2,5	6,0	2,5	-	10	12,0	22630.0570	
12	12	12	M4	15	12	3,0	8,0	3,0	-	12	21,0	22630.0572	
14	14	14	M4	17	14	3,5	8,0	3,5	-	14	34,0	22630.0574	
16	16	16	M5	20	16	4,0	10,0	4,0	-	16	51,0	22630.0576	
20	20	20	M5	25	20	5,0	10,0	5,0	-	20	101,0	22630.0580	
편평한 볼, 단차 없음 - 그림 4, 공구강													
5	5	5	M2,5	6	5	2,0	4,5	1,0	1,50	5	1,2	22630.0605	
6	6	6	M3	8	6	2,0	5,0	1,0	1,80	6	3,1	22630.0606	
8	8	8	M3	10	8	2,0	6,0	2,0	1,90	8	5,0	22630.0608	
10	10	10	M3	13	10	2,5	6,0	2,5	2,50	10	11,0	22630.0610	
12	12	12	M4	15	12	3,0	8,0	3,0	2,50	12	17,0	22630.0612	
14	14	14	M4	17	14	3,5	8,0	3,5	3,90	14	30,0	22630.0614	
16	16	16	M5	20	16	4,0	10,0	4,0	4,30	16	44,0	22630.0616	
20	20	20	M5	25	20	5,0	10,0	5,0	5,00	20	88,0	22630.0620	

d ₁ g6	d ₂ n6	d ₃ -0,01 -0,05	d ₄	치수						위치 홀 D ₁ H7	[g]	제품 번호
				l ₁	l ₂	l ₃	t	r	b			
[mm]										[mm]	[g]	
25	25	25	M5	25	25	6,0	10,0	6,0	5,60	25	149,0	22630.0625
30	30	30	M6	30	30	8,0	12,0	8,0	8,80	30	270,0	22630.0630
40	40	40	M6	40	40	10,0	12,0	10,0	12,80	40	657,0	22630.0640
50	50	50	M6	50	50	12,0	12,0	12,0	16,70	50	1243,0	22630.0650
편평한 볼, 단차 없음 - 그림 4, 스테인리스 스틸												
5	5	5	M2,5	6	5	2,0	4,5	1,0	1,50	5	1,1	22630.0665
6	6	6	M3	8	6	2,0	5,0	1,0	1,80	6	2,3	22630.0666
8	8	8	M3	10	8	2,0	6,0	2,0	1,90	8	5,0	22630.0668
10	10	10	M3	13	10	2,5	6,0	2,5	2,50	10	11,0	22630.0670
12	12	12	M4	15	12	3,0	8,0	3,0	2,50	12	17,0	22630.0672
14	14	14	M4	17	14	3,5	8,0	3,5	3,90	14	30,0	22630.0674
16	16	16	M5	20	16	4,0	10,0	4,0	4,30	16	44,0	22630.0676
20	20	20	M5	25	20	5,0	10,0	5,0	5,00	20	88,0	22630.0680

적용 예



규정 준수

RoHS 준수

지침 2011/65/EU 및 지침 2015/863 준수

SVHC 재질을 미포함

0.1% w/w 이상 함유된 SVHC 물질 없음 - 2024년 6월 27일 SVHC 목록.

식수안전 및 독성물질 관리법 물질을 포함하지 않음

식수안전 및 독성물질 관리법 물질들이 포함되어 있지 않음

<https://www.P65Warnings.ca.gov/>

분쟁 광물 포함하지 않음

이 제품은 탄탈륨, 주석, 금 또는 텅스텐 등 민주 공화국 또는 인접 국가에서 "분쟁 광물"로 지정된 물질을 포함하지 않습니다.