

Șuruburi plate moletate • DIN 653 EH 24770.



Descrierea produsului

Knurled thumb screws are very versatile. Three material versions for the different requirements

- steel, blackened
- steel, zinc-plated by galvanization
- stainless steel

are available.

Knurled thumb screws can be easily tightened and released by hand. The ribbed outer surface of the nut prevents slipping when tightening / releasing with the fingers.

Toate șuruburile moletate sunt produse dintr-o singură bucată cu filet până la cap (Clasa DIN A).

Material

- Oțel, brunat, calitatea 5.8
- Steel, zinc-plated by galvanization, quality 5.8
- Oțel inoxidabil 1.4305, sablare mată

Mai multe informații


Note

Înclinația filetului sau adâncimea poate să difere față de standardul DIN.

Produse asociate

- Șuruburi moletate înalte, DIN 464


Desen



Informații comandă

d ₁	l	Dimensiuni		k	[g]	Ref. Nr.
		d ₂	[mm]			
Oțel, brunat, calitatea 5.8						
M 3	6	12		2,5	2,3	24770.0072
M 3	8	12		2,5	2,4	24770.0073
M 3	10	12		2,5	2,5	24770.0074
M 3	16	12		2,5	2,7	24770.0077
M 3	20	12		2,5	2,9	24770.0079
M 4	8	16		3,5	5,6	24770.0092
M 4	10	16		3,5	5,7	24770.0093
M 4	12	16		3,5	6,1	24770.0094
M 4	16	16		3,5	6,2	24770.0096
M 4	20	16		3,5	6,6	24770.0098
M 4	25	16		3,5	7,1	24770.0100
M 5	10	20		4,0	10,0	24770.0112
M 5	12	20		4,0	11,0	24770.0113
M 5	16	20		4,0	12,0	24770.0115
M 5	20	20		4,0	12,0	24770.0117
M 5	25	20		4,0	12,0	24770.0119
M 5	30	20		4,0	13,0	24770.0121
M 6	12	24		5,0	18,0	24770.0132
M 6	16	24		5,0	20,0	24770.0134

d ₁	Dimensiuni			k	[g]	Ref. Nr.
	l	d ₂	[mm]			
M 6	20	24		5,0	21,0	24770.0136
M 6	25	24		5,0	21,0	24770.0138
M 6	30	24		5,0	22,0	24770.0140
M 6	40	24		5,0	23,0	24770.0142
M 8	16	30		6,0	36,0	24770.0152
M 8	20	30		6,0	37,0	24770.0154
M 8	25	30		6,0	39,0	24770.0156
M 8	30	30		6,0	40,0	24770.0158
M 8	35	30		6,0	42,0	24770.0160
M 8	40	30		6,0	44,0	24770.0161
M10	20	36		8,0	71,0	24770.0172
M10	25	36		8,0	72,0	24770.0174
M10	30	36		8,0	76,0	24770.0176
M10	35	36		8,0	78,0	24770.0178
M10	40	36		8,0	80,0	24770.0180
Oțel, zincat prin galvanizare						
M 3	6	12		2,5	2,0	24770.0472
M 3	8	12		2,5	2,0	24770.0473
M 3	10	12		2,5	3,0	24770.0474
M 3	16	12		2,5	3,0	24770.0477
M 3	20	12		2,5	3,0	24770.0479
M 4	8	16		3,5	6,0	24770.0492
M 4	10	16		3,5	6,0	24770.0493
M 4	12	16		3,5	6,0	24770.0494
M 4	16	16		3,5	7,0	24770.0496
M 4	20	16		3,5	7,0	24770.0498
M 4	25	16		3,5	7,0	24770.0500
M 5	10	20		4,0	10,0	24770.0512
M 5	12	20		4,0	11,0	24770.0513
M 5	16	20		4,0	12,0	24770.0515
M 5	20	20		4,0	12,0	24770.0517
M 5	25	20		4,0	14,0	24770.0519
M 5	30	20		4,0	13,0	24770.0521
M 6	12	24		5,0	19,0	24770.0532
M 6	16	24		5,0	19,0	24770.0534
M 6	20	24		5,0	20,0	24770.0536
M 6	25	24		5,0	20,0	24770.0538
M 6	30	24		5,0	20,0	24770.0540
M 6	40	24		5,0	23,0	24770.0542
M 8	16	30		6,0	35,0	24770.0552
M 8	20	30		6,0	38,0	24770.0554
M 8	25	30		6,0	35,0	24770.0556
M 8	30	30		6,0	35,0	24770.0558
M 8	35	30		6,0	43,0	24770.0560
M 8	40	30		6,0	40,0	24770.0561
M10	20	36		8,0	72,0	24770.0572
M10	25	36		8,0	74,0	24770.0574
M10	30	36		8,0	76,0	24770.0576
M10	35	36		8,0	76,0	24770.0578
M10	40	36		8,0	80,0	24770.0580
Oțel inoxidabil 1.4305						
M 4	8	16		3,5	5,6	24770.0292
M 4	10	16		3,5	5,7	24770.0293
M 4	12	16		3,5	6,1	24770.0294
M 4	16	16		3,5	6,2	24770.0296
M 5	10	20		4,0	10,0	24770.0312
M 5	12	20		4,0	11,0	24770.0313
M 5	16	20		4,0	12,0	24770.0315
M 5	20	20		4,0	12,0	24770.0317
M 6	12	24		5,0	18,0	24770.0332
M 6	16	24		5,0	20,0	24770.0334
M 6	20	24		5,0	21,0	24770.0336

d ₁	Dimensiuni			 [g]	Ref. Nr.
	l	d ₂	k		
M 6	25	24	5,0	21,0	24770.0338
M 8	16	30	6,0	36,0	24770.0352
M 8	20	30	6,0	37,0	24770.0354
M 8	25	30	6,0	39,0	24770.0356
M 8	30	30	6,0	40,0	24770.0358
M10	20	36	8,0	71,0	24770.0372
M10	25	36	8,0	72,0	24770.0374
M10	30	36	8,0	76,0	24770.0376
M10	40	36	8,0	80,0	24770.0380

Reclamație

Pentru detalii suplimentare despre conformitate, vă rugăm să selectați codul produsului dorit.